

PSS-650

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range	
Up/down position	300~375mm / 11 13/16~14 3/4 inches 475~625 mm / 18 11/16~24 19/32 inches (with Supplied extension pole) (25mm pitch adjustment)
Horizontal angle of rotation	± 10 deg
Left/right tilt angle	± 5 deg (Fine adjustment function with adjustment knob)
Up/down tilt angle	± 5 deg (Fine adjustment function with adjustment knob)
Front/back position	± 50 mm / ± 1 31/32 inches (Fine adjustment function with adjustment knob)
Left/right position	± 25 mm / ± 31/32 inch (Fine adjustment function with adjustment knob)
Dimensions (W x H x D)	
Dimensions (W x H x D)	299 x Height* x 453.5 mm / 11 25/32 x H x 17 27/32 inches *Height: 300~375mm / 11 13/16~14 3/4 inches 475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)
Dimensions (W x H x D) *without protrusions (Adjustment knob)	
Dimensions (W x H x D) *without protrusions (Adjustment knob)	246 x Height* x 322 mm / 9 11/16 x H x 12 11/16 inches *Height : 300~375mm / 11 13/16~14 3/4 inches 475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole)

Mass	
Mass	Approx. 8.6 kg / 19 lb
Maximum load	
Maximum load	30 kg / 66 lb
Optional accessories	
Optional accessories	PSS-650P
Color	
Color	Black

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.

Export PDF : October 8 2026