

## BC-L70A

Two-channel lithium-ion battery charger



### Overview

#### **Fast-charging, lightweight and compact**

The BC-L70A can charge the BP-FL75/FLX75 Olivine lithium-ion battery in only 65 minutes. It is also capable of simultaneous, continuous charging of up to two lithium-ion\* battery packs. The BC-L70A has the same light weight and compact dimensions as its predecessor, the BC-L70.

\* The BC-L70A cannot charge nickel metal hydride battery packs BP-M50 or BPM100.

### Features

#### **Efficient charging for two battery packs**

The BC-L70A features an advanced charging system that allows quick, efficient charging; up to two battery packs can be attached and charged simultaneously.

#### **Compact and lightweight**

The BC-L70A is compact, lightweight and easy to carry.

#### **Diagnostics functions**

The BC-L70A checks connected battery packs for abnormalities. Orange and green indicators will flash alternately if a battery pack cannot be charged normally.

#### **Charge progress indicator**

The orange indicator lights to show when a battery pack is charged less than 80%, and the green one when it is charged to 80% or more.

### Battery back-up

Should the AC power cord be accidentally unplugged from the AC power source, a charged lithium-ion battery pack attached to the BC-L70A provides an alternate back-up power to the connected device.

## Specifications

### Generic Specifications

|                               |   |
|-------------------------------|---|
| Power requirements            | AC 100 to 240 V, 50/60 Hz   |
| Power consumption             | Less than 168 VA  |
| DC output                     | Max, 16.8 V, 6A   |
| Operating temperature         | -20°C to +45°C (-4°F to +113°F)   |
| Dimensions (W x H x D)        | 60 x 237 x 134mm (2 3/8 x 9 3/8 x 5 3/8 inches)   |
| Mass                          | Approx. 1.2 kg (2lb 10oz)   |
| Charging time for one battery | BP-GL95B : 90mins<br>BP-GL95A : 135mins<br>BP-GL65A : 140mins<br>BP-FL75/FLX75 : 65mins |

## Supplied Accessories

|                  |     |
|------------------|-----|
| Plug Holder      | Yes |
| Operation Manuel | Yes |

### Related products



#### **BP-FLX75**

Olivine long-lasting battery with 76 Wh capacity



#### **BP-FL75**

Olivine long-lasting battery for F-series cameras



#### **BP-GL95A**

Lithium-ion battery pack 95 Wh capacity



#### **BP-L80S**

Rechargeable Lithium-ion Battery Pack

## Gallery

