

## CCFN-25

25 metre optical fibre hybrid cable with opticalCON connector



### Overview

**Used with the HXC-D70 multi-transmission studio camera system**

Optical fibre transmission for CA-FB70 and HXCE-FB70. 25m length cable.

**Power and optical fibre hybrid cable**

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

### Features

**Power and optical fibre hybrid cable**

Used with CCFN-JC1 coupler, doubles the distance between the HXC-D70 camera and the recording system.

### Related products



#### CA-FB70

Fibre adapter for HXC-D70 and PMW-320/350/400/500 camcorders



#### CA-TX70

Digital triax adapter for HXC-D70



#### HXC-P70

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fibre cable connection



#### HXC-FB80

Three 2/3-inch Exmor™ CMOS sensor HD colour studio camera

## Gallery

