

## ECM-680S

MS stereo shotgun Electret condenser microphone



### Overview

The Sony ECM-680S is an MS stereo\* shotgun, electret condenser-type microphone, ideal for a broad range of field production and broadcast studio applications. The ECM-680S offers excellent sensitivity, low inherent noise, and a flat-and wide frequency response. The most distinguished feature of the ECM-680S is its switchable operation between a highly directional monaural mode and stereo mode.

Monaural mode provides highly directional sound pickup, while stereo mode delivers natural and spatial sound. The ECM-680S is compact and lightweight, making it well-suited to use with a range of Sony professional camcorders. In addition, it can be mounted on a boom pole for more versatility. With its excellent quality and versatility, the ECM-680S is an ideal choice for quality-conscious sound gathering applications.

\* MS microphone signal of the ECM- 680S is internally decoded to L and R (stereo) outputs

### **Superior Sound Quality**

The ECM-680S uses the Mid-Side (MS) technique that offers natural stereo sound and excellent localization. Equipped with large diaphragm microphone capsules with bidirectional characteristics, the ECM-680S delivers a superb sensitivity of -28 dB\* (stereo)/-32 dB\* (monaural), and extremely low inherent

noise of less than 20 dB SPL (stereo/monaural).

\* 0 dB=1 V/Pa

### **Switchable between Stereo and Mono**

The ECM-680S can operate in either stereo or monaural (uni-directional) mode, allowing it to be used in both EFP and ENG applications. Stereo mode is ideal for capturing environmental sound with natural sound quality, while monaural mode is ideal for clearly capturing voice and sound from a distance. These modes can be selected from the switch on the microphone or from compatible Sony professional camcorders.

The LED on the microphone lights up when the ECM-680S is set to stereo mode, to easily notify the user that operating mode is currently selected.

### **Flat and Wide Frequency Response**

The ECM-680S microphone has a flat-and wide frequency response (50 Hz to 20 kHz (stereo)/40Hz to 20 kHz (monaural)) in both stereo and monaural modes, and will provide sound reproduction that is extremely smooth and natural.

### **Compact and Lightweight**

The ECM-680S has been designed to be a compact yet high-performance stereo shotgun microphone, ideal for camera mounted use. It measures only 250 mm (9 7/8 inches) in length and weighs less than 140 g (4.9 oz), maintaining good balance and mobility when mounted on a range of Sony professional camcorders.

## Specifications

### Audio Section

Capsule Type

Stereo MS Electret Condenser

Frequency Response	Stereo: 50 Hz to 20 kHz
Frequency Response	Monaural: 40 Hz to 20 kHz
Directivity	Stereo: Uni-directional
Directivity	Monaural: Super-cardioid
Sensitivity *[1]	Stereo: -28 dB $\pm$ 3 dB Monaural: -32 dB $\pm$ 3 dB
Output Impedance * [2]	100 $\Omega$ $\pm$ 20%, Balanced
Dynamic Range	Stereo: 104 dB or more Monaural: 106 dB or more
Signal-to-Noise Ratio *[3]	Stereo: 74 dB or more Monaural: 76 dB or more
Inherent Noise *[4]	Stereo: 21 dB SPL or less Monaural: 20 dB SPL or less
Induction Noise From External Magnetic Field *[5]	0 dB SPL or less
Wind Noise *[6]	60 dB SPL or less (with windscreen) 55 dB SPL (without windscreen)
Maximum Input Sound Pressure Level *[7]	124 dB SPL

## General Section

Connector	XLR-5-12C(male)
Mic Cable	XLR-5 pin to XLR-5pin (To connect with a Sony camcorder equipped with front 5-pin mic input connector) 380 mm 15 inches
Power Requirements	DC 40 V to 52 V
Dimensions *[8]	$\phi$ 20 x 250 mm $\phi$ 13/16 x 9 7/8 inches
Mass	Approx. 4.9 oz Approx. 105 g
Supplied Accessories	Windscreen (1) Stand screw adaptor (PF 1/2 thread - W 3/8 thread) (1) Stand screw adaptor (PF 1/2 thread - NS 5/8 thread) (1) Operating instructions (1) Microphone cable (LR-5-pin to LR-5-pin) (1) Mic spacer (2) Mic holder (1) Carrying case (1)

---

## Notes

- Note
- \*[1] 0 dB = 1 V/Pa, at 1 kHz
  - \*[2] Output impedance at 1 kHz
  - \*[3] A-weighted, 1 kHz, 1 Pa.
  - \*[4] 0 dB SPL = 20  $\mu$ Pa.
  - \*[5] dB SPL/1E-7 T, 0 dB SPL = 20  $\mu$ Pa.
  - \*[6] Wind noise at 2m/s (0 dB SPL = 20  $\mu$ Pa.)
  - \*[7] 0 dB SPL = 20  $\mu$ Pa.
  - \*[8] The values for dimensions are approximate.
-

## Gallery

