


## File Server mode License for FM2

\*Please contact your local sales representative for details.



### Overview

File Server mode License of FM2(FSL) is an option license of File Manager2.

The license enables standard file IO interface of File Manager2 and it can be usable by local or network applications (SMB).

Note: if you would like to use FSL, you must first install File Manager2 software and activate the File Manager2 license.

**This product is an activation key for pre-installed software.**

### Features

Enables File Server mode of File Manager2

### Specifications

Please review File Manager2 manual

### Related products



## ODS-D280U

Optical Disc Archive stand-alone drive with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



## ODS-D77UA

ODS-D77UA has very high transfer speeds. Read is 1.1Gbps. Write-once is 440 Mbps and Rewritable is 160 Mbps (verify on). Performance varies based on type of cartridge.



## ODS-D55U

Optical Disc Archive standalone drive unit with transfer speeds 330 Mbps (read) and 210 Mbps (write-once disc) or 130 Mbps (rewritable disc)



## ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



## ODS-L30M

\*Please contact your local sales representative for details.

## ODS-L60E

\*Please contact your local sales representative for details.

## ODS-L100E

\*Please contact your local sales representative for details.

## Optical Disc Archive Cartridge Generation 1

300GB\*, 600GB, 1.2TB and 1.5TB disc (Rewritable or Write once)  
 ODC300R, ODC300RE, ODC600R, ODC600RE, ODC1200RE, ODC1500R



## File Manager2

\*Please contact your local sales representative for details.

## ODS-L10

Optical Disc Archive 10-Slot library

## ODS-D380U

\*Please contact your local sales representative for details.

## Gallery

