

## ODBK-203

\*Please contact your local sales representative for details.



### Overview

**The ODBK-203 is a base unit of power supply for the ODS-L60E.**

**The ODBK-20X series can drive the ODS-D280F and the ODS-D77F.**

**A world of solutions**

### Related products



#### **ODS-L30M**

\*Please contact your local sales representative for details.



#### **ODS-L60E**

\*Please contact your local sales representative for details.



#### **ODS-L100E**

\*Please contact your local sales representative for details.



#### **ODS-D280F**

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge

## Gallery

