

## SCA-M30

High quality, ceiling microphone for IP security cameras.



### Overview

Microphones are a powerful addition to IP camera surveillance systems, adding an audio layer to the information captured by a security system. They can help draw an operator's attention to incidents or add meaning to an otherwise unintelligible scene. In monitored meetings or interrogations, a ceiling-mounted microphone adds an essential soundtrack to the video recording.

The SCA-M30 is an unobtrusive, indoor microphone which is optimised for capturing clear, high quality sound. Its high sensitivity is enhanced by physical protection against vibration and a filter to reject unwanted low-frequency noise.

Installation is easy, with a range of ceiling mounting options. It connects directly to Sony's IP cameras, which also supply the microphone's operating power.

### Features

#### **Highly Sensitive**

Capture even the quietest sounds with an extremely sensitive electret transducer.

#### **High Pass Filter to remove low frequency environmental noise**

A high pass filter blocks low frequency noise from fans, air conditioning, traffic, etc. improving the clarity of acquired audio.

## Housing minimises unwanted noise

Acoustic shielding suppresses noise from the sides and back of the microphone allowing effective pickup from the front.

## Simple to set audio pickup direction

Set the direction of maximum pickup by simply rotating the microphone protective grill.

## Scalable input sensitivity

The input sensitivity of the microphone is easily adjusted to the optimum level for specific installations.

## Easy to install

The microphone is easily installed recessed or projecting from a ceiling using only standard tools.

## Robust protective housing

The SCA-M30 is encased in a rubber protective shell which is also spring-mounted to minimise the effects of vibration.

## Related products



### SNC- VB635

Box-type 1080p/60 fps Camera with Half-inch Exmor™ CMOS Sensor Powered by IPELA ENGINE EX™ - V Series



### SNC- VB630

Box-type 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VB600

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM632R

Outdoor IR Ruggedized 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



### SNC- VM602R



### SNC- VM631



### SNC- VM630



### SNC- VM601

Outdoor IR  
Ruggedized 720p/60  
fps Camera Powered  
by IPELA ENGINE EX™  
- V Series

Vandal-resistant  
Minidome 1080p/60  
fps Camera Powered  
by IPELA ENGINE EX™  
- V Series

Minidome 1080p/60  
fps Camera Powered  
by IPELA ENGINE EX™  
- V Series

Vandal-resistant  
Minidome 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- VM600**

Minidome 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series

## Gallery

