

## SNC-UNI

Indoor fixed camera housing



### Overview

#### **13-inch indoor aluminium housing with clear window and hinged opening**

Tamper resistant camera housing with lock down screws provided. High strength steel wall mount bracket included.

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

### Features

#### **Flexible positioning**

Designed for mounting to a flat wall or round pole, larger than 3.5 inches in diameter.

#### **Supports a variety of cameras**

Network cameras accepted: SNC-CH120/140/220/240, SNC-ZB550, and SNC-EB520. analogue cameras accepted: SSC-FB530/560, SSC-G113A/213A and SSG-G103A/203A. Maximum camera/lens length should not exceed 9.5 inches.

### Related products



## **SNC- VB635**

Box-type 1080p/60 fps  
Camera with Half-inch  
Exmor™ CMOS Sensor  
Powered by IPELA  
ENGINE EX™ - V Series



## **SNC- VB630**

Box-type 1080p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **SNC- VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series

## **SNC- EB600**

Box-type 720p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series

## **SNC- EB630**

Box-type 1080p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series

## **SNC- EB520**

Box-type SVGA  
Camera - E Series

## Gallery

