

SNC-VM600L

Minidome 720p/60 fps Camera
Powered by IPELA ENGINE EX™ -
V Series



Overview

The SNC-VM600 minidome network camera delivers a new range of features and level of performance for an HD surveillance camera, with a maximum resolution of 1280 x 1024 pixels and improved sensitivity, thanks to a new Exmor CMOS sensor.

The SNC-VM600 features the IPELA ENGINE EX signal processing system, providing advanced features such as high frame rate, and improved image processing with View-DR, XDNR and DEPA Advanced. The high frame rate mode – 60 fps and 50 fps – delivers smoother, more natural movement in the video. View-DR at 130 dB captures objects clearly, even under very harsh lighting conditions, such as strong backlight or high contrast conditions. XDNR (eXcellent Dynamic Noise Reduction) delivers clear, low-noise, images in low light conditions. DEPA Advanced Intelligent Video and Audio Analytics triggers alarms according to user-defined rules. In-camera analytics are enhanced by additional features such as face detection, left object and removed object detection.

The camera SNC-VM600 offers a high sensitivity, with a minimum illumination of 0.05 lx in Colour mode and 0.04 lx in B/W mode. It can be powered by PoE (IEEE 802.3af-compliant), by AC 24 V +/- 20% or by DC 12 V +/- 10%, for easy installation.

Features

Excellent 720p/60 fps HD picture quality

Gain the huge surveillance benefits of excellent picture quality with 720p/60 fps HD, with up to 1280 x 1024 maximum resolution.

High quality and low noise images with Exmor CMOS sensor

Derived from Sony's broadcast range, the high resolution Exmor CMOS sensor improves image acquisition with its low noise characteristics.

Unique features from IPELA ENGINE EX signal processing system

IPELA ENGINE EX delivers high frame rate of up to 60 fps*, View-DR, XDNR (eXcellent Dynamic Noise Reduction) and DEPA Advanced Intelligent Video and Audio Analytics.

*Note: high frame-rate mode and ViewDR cannot be used at the same time.

DEPA delivers intelligent, customisable image capture and alarm triggering

The Sony DEPA platform offers intelligent video analytics, delivered through a combination of the intelligence built into the camera and the rules and filters that determine which images should be recorded and when an alarm should be triggered.

Operates at low minimum illumination

The SNC-VM600 operates at a minimum illumination of 0.05 lx in Colour mode (F1.2, View-DR OFF, VE OFF, AGC ON, 1/30 s, 30 fps) and 0.04 lx in B/W mode at 50 IRE and 30 fps.

Multiple video and audio codecs

The SNC-VM600 supports H.264 (High/Main/Baseline Profile) /JPEG video codecs and AAC (16 kHz/48 kHz)/G.726/G.711 audio codecs.

True Day/Night function for optimised images in all light conditions

Day/Night function automatically switches the camera between Day (colour) and Night (B/W) modes, depending on the light level. In Night mode, the IR-cut filter is removed so that the camera becomes sensitive to near-IR light and can reproduce images not visible to the naked eye.

ONVIF compliance for compatibility and confidence

The camera conforms to ONVIF (Open Network Video Interface Forum) Profile S, the widely-accepted protocol for information exchange between network video devices, giving you confidence in its breadth and ease of compatibility.

Specifications

| Camera | |
|-------------------------------|--|
| Image Sensor | 1/3-type progressive scan Exmor CMOS sensor |
| Number of Effective Pixels | Approx. 1.37 Megapixels |
| Signal System | NTSC/PAL (switchable) |
| Sync System | Internal synchronization |
| Minimum Illumination (50 IRE) | Color: 0.05 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.04 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) |

| | |
|----------------------------------|--|
| Minimum Illumination (30 IRE) | Color: 0.03 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) B/W: 0.02 lx (F1.2, View-DR Off, VE Off, AGC On, 1/30 s, 30 fps) |
| Dynamic Range | Equivalent to 130 dB with View-DR technology |
| S/N Ratio (Gain 0 dB) | More than 50 dB |
| Gain | Auto |
| Shutter Speed | 1/1 s to 1/10,000 s |
| Exposure Control | Exposure compensation, Shutter speed, Iris |
| White Balance | ATW, ATW-PRO, Fluorescent lamp, Mercury lamp, Sodium vapour lamp, Metal halide lamp, White LED, One push WB, Manual |
| Lens | Built-in varifocal lens |
| Easy Zoom | Yes |
| Zoom Ratio | Optical zoom 3x Digital zoom 4x Total zoom 12x |
| Easy Focus for Setup | Yes |

| | |
|----------------------------------|--------------------------------------|
| Horizontal Viewing Angle | 92.9° to 31.8° |
| Vertical Viewing Angle | 73.1° to 25.5° |
| Viewing Tilt Angle | 121.5° |
| Focal Length | f = 3.0 mm to 9.0 mm |
| F-Number | F1.2 (Wide) to F2.1 (Tele) |
| Minimum Object Distance | 300 mm |
| Pan/Tilt/Rotation Angle (manual) | ±192° -7° to +75° -99° to +99° |

Camera Features

| | |
|----------------------------------|-----------|
| Day/Night | True D/N |
| Day/Night linked with Easy Focus | Yes |
| e-Flip | Yes |
| Image rotate | 90°, 270° |
| Mirroring | Yes |
| Wide-D | View-DR |

| | |
|-----------------------------------|---|
| Tone Correction | Visibility Enhancer |
| Noise Reduction | XDNR |
| Image Stabilizer | Electronic |
| Picture Mode | Yes |
| Privacy Masking (number) | 20 |
| Privacy Masking (shape) | Quadrangle formed by any four corner points |
| Privacy Masking (color/effect) | Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic |
| Edge Storage | No |
| Voice Alert | Yes |
| Superimpose Number | 3 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo mark |
| Superimpose Language | English |
| | English, Japanese, Chinese (simplified), Chinese (traditional), |

| | |
|---------------|--|
| Menu Language | French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai |
|---------------|--|

| | |
|-------------------|-----|
| Smartphone viewer | Yes |
|-------------------|-----|

Video

| | |
|------------|--|
| Resolution | 1280 x 1024, 1280 x 960, 1024 x 768, 1280 x 720, 800 x 600, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 352 x 288, 320 x 240 (H.264, JPEG) |
|------------|--|

| | |
|--------------------|--|
| Compression Format | H.264 (High/Main/Baseline Profile), JPEG |
|--------------------|--|

| | |
|--------------------|---|
| Maximum Frame Rate | H.264: 60 fps (1280 x 1024) JPEG: 60 fps (1280 x 1024) |
|--------------------|---|

| | |
|----------------------|----------------------|
| Bitrate Control Mode | CBR/VBR (selectable) |
|----------------------|----------------------|

| | |
|---------------------------|--------------------|
| Range of Bit Rate Setting | 64 Kbps to 32 Mbps |
|---------------------------|--------------------|

| | |
|-----------|-----|
| Solid PTZ | Yes |
|-----------|-----|

| | |
|-----------------------|-------|
| Adaptive Rate Control | H.264 |
|-----------------------|-------|

| | |
|-------------------|------|
| Bandwidth Control | JPEG |
|-------------------|------|

| | |
|----------------------------|---------|
| Multi streaming Capability | Yes (3) |
|----------------------------|---------|

Number of Clients 20

Intelligent Video/Audio Analytics

Analytics Architecture DEPA Advanced

Intelligent Motion
Detection Yes

Face Detection Yes

Tamper Alarm Yes

Scene Analytics Passing, Intrusion, Left Object
Detection, Removed Object
Detection

Audio

Compression Format G.711/G.726/AAC (16 kHz, 48 kHz)

System Requirements

Operating System Windows XP (32 bit) Professional
Edition
Windows Vista (32 bit) Ultimate,
Business Edition
Windows 7 (32/64 bit) Ultimate,
Professional Edition
Windows 8 Pro (32/64 bit)

| | |
|--------------------|---|
| | Windows 8.1 Pro (32/64 bit) |
| Processor | Intel Core i7 2.8 GHz or higher |
| Memory | 2 GB or more |
| Web Browser | Microsoft Internet Explorer Ver. 7.0, Ver. 8.0, Ver. 9.0, Ver. 10.0, Ver. 11.0 Firefox Ver. 19.02 (plug-in free viewer only) Safari Ver. 5.1 (plug-in free viewer only) Google Chrome Ver. 25.0 (plug-in free viewer only) |
| SNC toolbox | Yes |
| SNC toolbox mobile | Yes |

Network

| | |
|--------------------------|---|
| Protocols | IPv4, TCP, UDP, ARP, ICMP, IGMP*, HTTP, DHCP, DNS, NTP, RTP/RTCP, RTSP over TCP, SMTP over HTTP, IPv6, HTTPS, FTP (client), SNMP (v1, v2c, v3), SSL *SSM (Source Specific Multicast) is supported. |
| Number of IP Address/Mac | 1 |

ADDRESS

| | |
|-----------------------------|------------|
| QoS | DSCP |
| Multicast Streaming Support | Yes |
| ONVIF Conformance | Profile S |
| Authentication | IEEE802.1X |

Interface

| | |
|---------------------------------|--|
| Analog Video Output | BNC x1, 1.0 Vp-p, 75 Ω, unbalance, sync negative 600 TV lines (analog video) *1 |
| Analog Monitor Output for Setup | Phono jack x1 |
| Microphone Input | Mini jack (monaural) |
| Line Input | Mini jack (monaural) |
| Line Output | Mini jack (monaural) Maximum output level: 1 Vrms |
| Network Port | 10BASE-T/100BASE-TX (RJ-45) |
| Alarm Input (Sensor Input) | x2, make contact, break contact x2, AC 24V/DC 24 V, 1 A |

| | |
|--------------|--|
| Alarm Output | (mechanical relay outputs electrically isolated from the camera) |
|--------------|--|

General

| | |
|--------------------|---|
| Power Requirements | IEEE 802.3af compliant (PoE system), DC 12 V \pm 10%, AC 24 V \pm 20% |
|--------------------|---|

| | |
|-------------------|------------|
| Power Consumption | 6.0 W max. |
|-------------------|------------|

| | |
|-----------------------|---------------------------------|
| Operating Temperature | -10°C to +50°C 14°F to 122°F |
|-----------------------|---------------------------------|

| | |
|------------------------|-------------------------------|
| Cold Start Temperature | 0°C to +50°C 32°F to 122°F |
|------------------------|-------------------------------|

| | |
|---------------------|--|
| Storage Temperature | -20 °C to + 60 °C -4 °F to + 140 °F |
|---------------------|--|

| | |
|--------------------|--------------|
| Operating Humidity | 20 % to 80 % |
|--------------------|--------------|

| | |
|------------------|--------------|
| Storage Humidity | 20 % to 95 % |
|------------------|--------------|

| | |
|---------------|---|
| Dimensions *2 | ϕ 148 x 108 mm ϕ 5 7/8 inches x 4 3/8 inches |
|---------------|---|

| | |
|------|-------------------------------------|
| Mass | Approx. 760 g Approx. 1 lb 11 oz |
|------|-------------------------------------|

| | |
|----------------------|--|
| External Material | Top cover: ABS + PC Dome cover: PC |
| External Color | Top cover: Munsell 4.4BG 8.4/0.2 |
| Fire Retardant | UL2044 |
| Safety Regulations | JATE Technical standard (LAN) UL2044, IEC60950-1 (CB) VCCI (Class A), FCC (Class A), IC (Class A) Emission: EN55022 (Class A) + EN50130-4 Immunity: EN55022 (Class A) + EN55024 Emission: AS/NZS CISPR22 (Class A) KCC EMC-TR |
| Supplied Accessories | CD-ROM (supplied programs) (1) Installation Manual (1) Template (1) Audio cable (1) I/O cable (1) BNC cable (1) Power input cable (1) Screw M3 (1) Bracket (1) Wire rope (1) |

Safety regulations (1)

| | |
|----------------------|--|
| Optional Accessories | YT-ICB600 (In-ceiling Bracket) YT-LD600S (Smoke Dome Cover) |
|----------------------|--|

Notes

*1 Monitor display ratio 4:3

*2 The values for dimensions are approximate.

Related products



UNI-MDPDH120

Pendant mount for indoor E Series and V Series minidome cameras



UNI-BBB1

Wall/pole mount adapter box for Sony SNC-CH outdoor series video security cameras



UNI-UMB1

Indoor wall mounting bracket for minidome and PTZ cameras

Gallery

