

## SR-D1

SRMASTER compact memory  
drive unit



### Overview

#### **Compact SRMemory drive unit for use with PCs**

The SR-D1 compact SRMemory drive allows you to view and import full resolution SRMASTER content.

PCs with SR-D1 driver software installed can be connected to the SR-D1 via USB3.0 or eSATA. A dedicated F65RAW /SR viewer can be used to review and transfer pictures from SRMemory media.

### Features

#### **Low cost, compact design**

Compact and lightweight design for use on the desktop or location. The lowest cost drive in the SRMASTER family, the SR-D1 is designed to bring the benefits of SRMASTER and F65 workflow to a wider audience, including for on-set dailies and post production.

#### **Supports HD SStP and F65RAW formats**

The SR-D1 supports both RGB HD 10-bit MPEG-4 SStP and 16-bit linear F65RAW formats. The unit works with SRMemory cards recorded using an F65 with the SR-R4 recorder and is also ideal for users of cameras such as the PMW-F3 for shooting at the highest quality with the SR-R1.

#### **Supports USB3.0 and eSATA interfaces**

The unit supports USB 3.0 and eSATA interfaces for high-speed

file transfer. Shortening the waiting time during ingest.

### Direct access files on SRMemory media

Provides direct access to files on SRMemory media. Files can be selected and viewed via the network before transfer. It features Drag & Drop file transfer for ease of use.

### AC / DC operation for operational flexibility

The SR-D1 is equally at home in the field or on the desktop, supporting both DC operation and with an AC adaptor supplied.

## Specifications

### General

Power Requirements	12 V DC
Power Consumption	30 W (maximum)
Operating Temperature	5°C to 40°C 41°F to 104°F
Storage Temperature	-20°C to +60°C -4°F to +140°F
Mass	1.5 kg 3 lb 4 oz
Dimensions (W x H x D) *1	154 x 49 x 227mm (excluding protrusion) 6 1/8 x 1 15/16 x 9 inches (excluding protrusion)

### Input/Output

---

USB	Hi-Speed USB (USB2.0 compliant)/SuperSpeed USB (USB3.0 compliant)
eSATA	eSATA 1.0/eSATA2.0

---

## Supplied Accessories

Supplied Accessories	AC adapter (1) USB cable (1) Rubber feet (4) Operation manual (J, E, CN) (1)
----------------------	---

---

## Notes

Note	*1 The values for dimensions are approximate.
------	---

---

## Gallery

