

## SF-M Series UHS-II SD Memory Card

Effortless efficiency. Shoot and transfer 4K video quickly and easily. Ideal for video shooting with professional camcorders.



### Overview

#### **Efficient workflow**

Transfer large-sized video files quicker and start editing sooner with an ultra-fast read speed of up to 277 MB/s.

#### **Total reliability and enhanced durability**

Sony SF-M series memory cards are tested for durability in a range of shooting conditions and deliver reliable performance wherever you are. Our cards are built to withstand drops and shocks in hot, cold and wet conditions so you can shoot with confidence.

#### **Free “SD Scan Utility” and “File Rescue” software**

“SD Scan Utility” scans your SD card and tells you before it reaches its write-cycle limit.

With “File Rescue” software you can quickly and simply recover lost data.

2 invaluable applications that are available as free download.

### Features

#### **Stable 4K video shooting**

A fast write speed up to 150MB/s enables professional grade video shooting - and V60 of Video Speed Class supports camcorders requiring higher video quality based on V60.

#### **Efficient Workflow**

Sony SF-M Series memory cards allow users to transfer large-sized video files quicker and start editing sooner with an ultra-fast read speed of up to 277 MB/s.

### **Free SD Scan Utility**

Over time, SD cards wear out and stop recording reliably. SD Scan Utility scans your SD card and tells you before it has reached its write-cycle limit. Available as free download for Sony memory card customers.

### **Free File Rescue**

One small slip and precious footage and files can accidentally be deleted. With our powerful File Rescue software you can quickly and simply recover lost data. Downloaded it for free when you buy a Sony memory card.

### **Fully compatible with Sony camcorders**

Sony SF-M Series cards are built for compatibility with Sony camcorders, giving serious flexibility to shoot with range of camcorders and cameras.

### **Speed up with the MRW-S1\*1 reader writer.**

Transfer large-sized files quickly with the MRW-S1 reader writer. With the fast memory card reader MRW-S1, UHS-II SD cards like SF-M series can be read at a faster speed.

\*1 Required to connect to the USB3.1 Gen 1 port on your PC.

## Specifications

### Size & Weight

DIMENSIONS (W X H X D)	24 x 32 x 2.1 mm
------------------------	------------------

WEIGHT	2 g
--------	-----

## General Features

CAPACITY	SF-M64: 64GB SF-M128: 128GB SF-M256: 256GB SF-M64: 57.6GB SF-M128: 115.2GB SF-M256: 230.4GB
INTERFACE	UHS-II
TRANSFER SPEED (READ)	Up to 277MB/s (HD312), Up to 95MB/s (SDR104)
TRANSFER SPEED (WRITE)	Up to 150MB/s (HD312), Up to 90MB/s (SDR104)
SPEED CLASS	Class10 (SD Speed Class) U3 (UHS Speed Class)

## Gallery

