

ECM-44BMP

Affordable omni-directional lapel microphone



Overview

Sony has produced over five million professional ECM (Electret Condenser Microphones) microphones and the ECM-44 is the affordable, general voice model. It provides good sound quality and is widely used in business presentation systems and TV production. The ECM-44 is available in four versions, featuring different connector types. This model, ECM-44BMP, has a 3.5mm locking jack for use with the UWP and UWP-D bodypack transmitters (excluding UTXB03HR).

Convenient to use

The ECM-44 is an affordable alternative to the traditional hand held microphone and being 'hands free' it allows the presenter to concentrate on her/his performance

Professional image

Either 'in front of camera' or at a business presentation the ECM-44 creates a professional and tidy image.

Easy to use

It can often be difficult to achieve good quality voice pick-up but the ECM-44 can help get good results. The microphone's capsule is designed for general voice pick-up with a mid-frequency emphasis characteristic and a suitable frequency response.

Features

Tuned for voice pick-up

The ECM-44's capsule features an emphasis curve and a suitable frequency response for voice pick-up.

Compact size

The capsule has a diameter of only 8.5mm and is 14.5mm long.

Ready for wireless systems

The ECM-44BMP is compatible with the Sony UWP and UWP-D bodypack transmitters.

Specifications

Audio Section

| | |
|---|-----------------------|
| Capsule Type | Electret Condenser |
| Frequency Response | 40 Hz to 15 kHz |
| Directivity | Omni-directional |
| Sensitivity *[1] | -40.0 dB (10 mV) |
| Output Impedance * [2] | 2.5kΩ±30%, Unbalanced |
| Dynamic Range | 90 dB or more |
| Signal-to-Noise Ratio *[3] | 62 dB or more |
| Inherent Noise *[4] | 32 dB SPL or less |
| Induction Noise From External Magnetic | 5 dB SPL or less |

Field *[5]

Wind Noise *[6] 40 dB SPL or less (with windscreen)

Maximum Input
Sound Pressure Level 122 dB SPL
*[7]

General Section

Connector BMP type. Supplied with ø3.5 mm, 3-pole mini plug.

Mic Cable 3.9 feet
1.2 m

Power Requirements DC 1.1 V to 10.0V

Power Consumption 0.4 mA or less

Dimensions *[8] ø8.5 x 14.5 mm (Mic head)
ø11/32 x 19/32 inches (Mic head)

Mass Approx. 18 g
Approx. 0.6 oz

Supplied Accessories Urethane type windscreen (1)
Single/horizontal type tie clip (1)
Operating instructions (1)
Mic case (1)

Wind screen pack

Notes

Note

- *[1] 0 dB = 1 V/Pa, at 1 kHz
- *[2] Output impedance at 1 kHz
- *[3] A-weighted, 1 kHz, 1 Pa.
- *[4] 0 dB SPL = 20 μ Pa.
- *[5] dB SPL/1E-7 T, 0 dB SPL = 20 μ Pa.
- *[6] Wind noise at 2m/s (0 dB SPL = 20 μ Pa.)
- *[7] 0 dB SPL = 20 μ Pa.
- *[8] The values for dimensions are approximate.

Related products



UWP-D21

UWP-D bodypack wireless microphone package



UWP-D22

UWP-D handheld wireless microphone package



UWP-D26

UWP-D bodypack transmitter and XLR plug-on wireless microphone transmitter package



UWP-D11

UWP-D bodypack wireless microphone package



UWP-D12

UWP-D handheld
wireless microphone
package

Gallery

