

## F-720

Uni-directional dynamic microphone



### Overview

**For general presentation and speech use in schools, halls, churches and other industrial applications**

Virtually impervious to handling noise and vibration because of efficient, one-piece capsule shock mount.

#### **TALK switch**

Turns the microphone on and off.

### Features

#### **TALK switch**

Convenient TALK switch to turn the microphone on and off

### Specifications

#### Audio Section

Capsule Type	Dynamic
--------------	---------

Frequency Response	50 Hz to 13 kHz
--------------------	-----------------

Directivity	Uni-Directional
-------------	-----------------

Sensitivity *[1]	-57 dB $\pm$ 3 dB
------------------	-------------------

Output Impedance * [2]	500Ω ± 20%, Balanced
---------------------------	----------------------

Induction Noise From External Magnetic Field *[3]	10 dB SPL or less
---	-------------------

Wind Noise *[4]	Less than 55 dB SPL
-----------------	---------------------

## General Section

Connector	XLR-3-12C (male)
-----------	------------------

Power Requirements	No power required
--------------------	-------------------

Dimensions *[5]	o37.6 x 160 mm o1 1/2 x 6 3/8 inches
-----------------	---

Mass	Approx. 9.2 oz Approx. 260 g
------	---------------------------------

Supplied Accessories	Stand adaptor (PF 1/2 to W 3/8) (1) Stand adaptor (PF 1/2 to NS 5/8) (1) Operating instructions (1) Microphone holder (PF 1/2) (1)
----------------------	--

## Notes

\*[1] 0 dB = 1 V/Pa, at 1 kHz

\*[2] Output impedance at 1 kHz

Note

\*[3] dB SPL/1E-7 T, 0 dB SPL = 20? Pa.

\*[4] Wind noise at 2m/s (0 dB SPL = 20?Pa.)

\*[5] The values for dimensions are approximate.

---

## Gallery

