


FW-100BZ40J

Our 100" premium 4K Ultra HD HDR professional display with Cognitive Processor XR™



Overview

The 100" BRAVIA FW-100BZ40J combines bright, beautiful 4K pictures with business-friendly features.

Featuring Sony's powerful Cognitive Processor XR, the FW-100BZ40J delivers superb picture quality, with immersive images that combine amazing colour, contrast and clarity. The screen's Cognitive Processor XR uses cognitive intelligence to deliver sound and imagery optimised for human ears and eyes. The FW-100BZ40J also achieves high brightness of 600-nit (typical)/940-nit (peak) by Full Array Local Dimming backlight.

The robust and rigid FW-100BZ40J is designed with a wide range of B2B applications in mind, thanks to a symmetrical four-sided aluminium bezel and a carrying handle providing ease of mobility.

The display's powerful built-in Android OS System on an SoC platform ensures fast boot-up plus smooth apps, animations and a seamless user experience.

Pro mode allows quick and easy customisation to suit different environments including corporate, education and digital signage, while One Step Setting optimises set-up for signage and conference rooms at the touch of a button. IP control capability allows easy installation with support from major key partners including Crestron, Extron and Kramer. The FW-100BZ40J also features integrated mirroring functionality through both Chromecast built-in and AirPlay2, providing a simple, quick and touchless connection from a user's device.

For even greater peace of mind there's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Features

Cognitive Processor XR

When the different elements that make up a display picture are looked at individually and all elements adjusted to the same level, the results can feel artificial and take the viewer out of the experience. Using human perspective analysis, the Cognitive Processor XR cross-analyses thousands of elements at once to create the perfect immersive picture, just as if it was happening in reality.

Rich, natural colour with XR TRILUMINOS Pro

Powered by our Cognitive Processor XR, our FW-100BZ40J display reproduces colour in a way that human eye finds beautiful. See a wider palette of colours with an enhanced range of hue and saturation, allowing natural shades and precise details to be seen, even in dark scenes.

Spectacular brightness and contrast

With a peak brightness of 940cd/m² (600cd/m² typical), the panel

has Full Array Local Dimming (FALD), making it ideal for presenting 4K HDR (High Dynamic Range) content and revealing subtle detail in bright highlights and areas of dark shadow.

See finer detail with XR upscaling

The FW-100BZ40J accesses and utilises a vast amount of data, analysing patterns in scenes and recreating subtle details to upscale 2K signals close to true 4K quality for incredibly real and immersive viewing.

Smooth, fluid on-screen action XR Motion Clarity

On some screens, especially large ones, fast-moving scenes can lead to blur. Our latest LED XR X-Motion Clarity™ technology keeps everything smooth, bright and clear. Each frame is individually controlled and its duration optimised, while brightness is boosted when needed, so you won't miss a thing.

Simple screen mirroring

Support for Chromecast built-in and Apple AirPlay2 makes it easy to stream AV content wirelessly from an Android or iOS device straight to BRAVIA.

Enhanced wireless connectivity

The FW-100BZ40J supports wireless connectivity via Wi-Fi 5GHz and 2.4GHz as well as Bluetooth 4.2.

Made for doing business

The FW-100BZ40J is designed for professional installations with a robust design, support for landscape, portrait or tilt orientation plus a rugged integral carry handle and cable clamber.

Developer friendly, easy integration

BRAVIA offers seamless support with leading automation and control platforms, while open APIs offer limitless integration opportunities with other vendor solutions.

Greater Peace of Mind

There's the added reassurance of our 3 Years warranty with Repair or if necessary advanced exchange handled by local partner, on premise where possible. You can also choose to extend your support for an additional 2 years.

Specifications

Display Features

| | |
|------------------------|---------------------|
| Brightness (cd/m2) | Typ. 600 / Peak 940 |
| Native Contrast Ratio | 9000:1 |
| Dynamic Contrast Ratio | 600,000:1 |
| Response Time (ms) | 7 |
| Panel type | VA |
| Dimming Type | Local Dimming |
| Display Device | LCD |
| Backlight Type | Direct LED |
| Operation Time | 24/7 |
| Portrait Mode | Yes |

Display Specifications

Screen Size for WEB
(diagonal, cm, integer) 253cm

or 1st decimal)

| | |
|---|--------------------|
| Display resolution (H x V, pixels) | 3840 x 2160 |
| Screen Size (inch, measured diagonally) | 100" (99.5") |
| Viewing Angle (Right/Left/Up/Down) | 178 (89/89) degree |
| Display Resolution | QFHD |
| Aspect Ratio | 16:09 |

Professional Features

| | |
|--|------|
| HDMI Auto Wake-up | Yes |
| Multicast/IPTV | Yes |
| Compatible with TDM Digital Signage/TEOS Solutions | Yes |
| On-board Storage (GB) | 16GB |

Network Features

| | |
|--------------|-----|
| Wi-Fi Direct | Yes |
|--------------|-----|

| | |
|-----------------------------------|--|
| Wi-Fi Certified | Yes |
| Wi-Fi Standard | a/b/g/n/ac |
| Wi-Fi Frequency | 2.4GHz/5GHz (for Wi-Fi Direct: 2.4GHz Only) |
| Codec for Home Network | MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC / JPEG |
| Apple AirPlay (Internet required) | Yes |
| Chromecast built-in | Yes |
| Wireless LAN | Integrated |
| Application Store | Yes (Google Play Store) |

Convenience Features

USB Playback Codecs

MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS
 (HDV,AVCHD):MPEG2,AVC / MP4
 (XAVCS):AVC,MPEG4,HEVC /
 AVI:Xvid,MotionJpeg / ASF
 (WMV):VC1 /
 MOV:AVC,MPEG4,MotionJpeg /
 MKV:Xvid,AVC,MPEG4,VP8.HEVC /
 WEBM:VP8 / 3GPP:MPEG4,AVC /
 MP3 / ASF (WMA) / LPCM / WAV /
 MP4AAC / FLAC / JPEG

HDMI-CEC Yes

On Screen Clock Yes

Sleep Timer Yes

On/Off Timer Yes

Display Language

AFR, AMH, ARA, ASM, AZE, BEL,
 BUL, BEN, BOS, CAT, CZE, DAN,
 DEU, GRE, ENG, SPA, EST, BAQ,
 PER, FIN, FRA, GLG, GUJ, HIN, HRV,
 HUN, IND, ISL, ITA, HEB, JPN, KAZ,
 KAN, KOR, KIR, LAO, LIT, LAV, MAC,
 MAL, MON, MAR, MAY, BUR, NOB,
 NEP, NLD, ORI, PAN, POL, POR,
 RUM, RUS, SOL, SLV, ALB, SRP,
 SWE

Control Specs

| | |
|------------|-----|
| IP Control | Yes |
|------------|-----|

| | |
|-----------------|----------|
| RS-232C Control | 1 (Side) |
|-----------------|----------|

| | |
|----------|-----|
| Pro mode | Yes |
|----------|-----|

Inputs & Outputs

| | |
|-------------|---|
| HDMI Signal | 4096x2160p(24,50,60Hz), 3840x2160p(24,25,30,50,60Hz), 1080p(30,50,60,100,120Hz), 1080/24p, 1080i(50,60Hz), 720p(30,50,60Hz), 720/24p, 576p, 480p |
|-------------|---|

| | |
|------|---------------------------|
| HDCP | HDCP2.3 (for HDMI1/2/3/4) |
|------|---------------------------|

| | |
|----------------|------------------|
| AC Power Input | C18 INLET (REAR) |
|----------------|------------------|

| | |
|--------------------------|----------|
| Composite Video Input(s) | 1 (Side) |
|--------------------------|----------|

| | |
|-------------------|----------|
| HDMI Inputs Total | 4 (Side) |
|-------------------|----------|

| | |
|-------------------------|----------|
| Digital Audio Output(s) | 1 (Side) |
|-------------------------|----------|

| | |
|---------------------|----------|
| Headphone Output(s) | 1 (Side) |
|---------------------|----------|

| | |
|-----------|----------|
| USB Ports | 2 (Side) |
|-----------|----------|

| | |
|-----------------|----------|
| Ethernet Inputs | 1 (Side) |
|-----------------|----------|

| | |
|------------------|----------|
| RS-232C Input(s) | 1 (Side) |
|------------------|----------|

Audio Specifications

| | |
|------------------|-------------|
| Speaker Position | Down Firing |
|------------------|-------------|

| | |
|--------------------|-----------|
| Audio Power Output | 10W + 10W |
|--------------------|-----------|

| | |
|---------------------------------------|---|
| Digital Audio Out (Optical) Format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, DTS |
|---------------------------------------|---|

| | |
|-------------|-----|
| Dolby Atmos | Yes |
|-------------|-----|

| | |
|----------------|--|
| Speaker Type-2 | Sound Positioning, X-Balanced Speaker |
|----------------|--|

| | |
|-------------|-----|
| Clear Phase | Yes |
|-------------|-----|

| | |
|-------------------------------|--------------------------|
| Dolby Audio Format Support | Dolby Audio, Dolby Atmos |
|-------------------------------|--------------------------|

| | |
|------------------------------------|-----------|
| HDMI Audio Return Channel (ARC) | Yes (ARC) |
|------------------------------------|-----------|

| | |
|----------------------------|--|
| HDMI Input Audio Format | 5.1 channel linear PCM: 32/44.1/48/88.2/96/176.4/192kHz 16/20/24bits, Dolby Audio, Dolby Atmos, DTS |
|----------------------------|--|

| | |
|-------------------|--|
| ARC Output Format | Two channel linear PCM: 48kHz 16bits, Dolby Audio, Dolby Atmos, |
|-------------------|--|

DTS

Video Specifications

| | |
|--|------------------------------------|
| Wide Mode | Wide zoom/Normal/Full/Zoom/14:9 |
| 4:3 Default | Yes |
| Video Processing | 4K X-Reality PRO |
| Motion Enhancer | X-Motion Clarity, Auto mode |
| 4K Processor | XR Processor |
| HDR (High Dynamic Range) compatibility | Yes (HDR10, HLG, Dolby Vision) |
| Panel Refresh Rate (Native Hertz) | 100Hz/120Hz |

Design Features

| | |
|-------------------------------|-------------------|
| Cable Management | Yes |
| Frame color | Black |
| Stand Design | Metal Blade Stand |
| VESA® Hole Spacing Compatible | Yes |
| VESA® Hole Pitch (W x | |

H) 60.0 x 40.0 cm

Eco & Energy saving

EEA SDR RANK G

Power Consumption
(in Standby) 0.50W

Mercury Content (mg) 0

Power Saving Mode /
Back Light Off Mode Yes

Power Requirements
(voltage) AC 220-240V

Dimensions

Screen Size (inch,
measured diagonally) 100" (99.5")

Screen Size for WEB
(diagonal, cm, integer
or 1st decimal) 253 cm

Dimension of Package
Carton (W x H x D) Approx. 244.0 x 157.7 x 37.8 cm

Weights (Approx.)

Weight of TV without Stand Approx. 88.9 kg

TV with Stand
(Standard position) Approx. 92.6 kg

Weight of Package
Carton (Gross) Approx. 129 kg

Related products



BRAVIA Signage Free

Standalone simple digital signage (Free)

Gallery

