

FW-75BZ40H

75" 4K Ultra HD HDR
Professional Display



Overview

Present a better image for your business

Optimised for professional use, the slim, energy-efficient FW-75BZ40H combines bright 4K HDR image quality with easy operation, flexible networking/control and extensive integration options.

Every 4K Professional Display takes full advantage of latest consumer television technologies to ensure vibrant, high-brightness 4K HDR images that add impact to all your content. Beautiful pictures are balanced by Acoustic Multi-Audio™ for clear, immersive sound.

The FW-75BZ40H is designed for dependable 24/7 operation in a wide range of B2B applications. Side-mounted terminals allow easy access for cable connections. The display's elegantly minimal design is enhanced further for professional use with a four-sided aluminium bezel and full protective rear.

Pro mode allows quick and easy customisation to suit different environments including corporate, education and hospitality, while One Step Setting optimises display settings for signage and conference rooms at the touch of a single button. A powerful SoC platform with improved processing speeds allow apps and animation to run smoothly and efficiently alongside a stress-free

user interface for easy operation.

Creating attractive digital signage is simple, mixing and displaying media files and online content with no need for additional hardware. The display's Android platform broadens control and customisation options, while a wide range of API (Application Programming Interface) options enable remote control/monitoring and integration with external systems.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

Very high brightness and contrast

The high brightness, high contrast panel with Full Array local dimming is ideal for presenting 4K HDR (High Dynamic Range) content, revealing subtle detail in bright highlights and areas of dark shadow.

See finer detail

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution picture sources.

Rich, natural colour with TRILUMINOS Display

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of more vivid, lifelike hues and tones.

Smooth, fluid on-screen action

X-Motion Clarity™ ensures smoother, more natural reproduction of rapidly-moving on-screen images.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy easily to multiple displays via USB flash memory.

One Step Setting

A time-saver in corporate environments, One Step Setting optimises picture and networking settings to suit meeting rooms and signage applications at the touch of a single button.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage. Combine graphics, text, video and live web content to create attractive signage in minutes with no extra hardware or special training.

Reliable 24/7 operation

Engineered for dependable round-the-clock operation in the most demanding corporate and AV presentation environments.

Cast content with Apple AirPlay2

With Apple AirPlay2 it's easy to stream video and sound right from an iPhone, iPad or Mac.

Google Chromecast built in

Cast videos and apps from a mobile device directly with Google Chromecast. Just tap the Cast button on your Android or iOS device screen and instantly enjoy super-sized on.

Versatile remote control

Control remotely – including on/off, input signal select and adjust volume – over IP via RJ45 by web API or via RS-232C.

Connectivity when you need it most

The FW-75BZ40H supports Wi-Fi 5GHz and 2.4GHz as well as Bluetooth 4.2.

Flexible mounting and installation

The display offers flexible mounting options (vertical, tilt, and table-top), with VESA-standard mounting for easy integration into a wide range of environments.

Specifications

Display Features

| | |
|---|-------------------------------|
| Dimming Type | Local Dimming |
| Display Device | LCD |
| Backlight Type | Direct (Full Array LED) |
| Brightness (cd/m ²) (*1) | 620 (Peak Brightness: 850 *1) |
| Contrast Ratio (*1) | 6000:1 |
| Dynamic Contrast Ratio | 600000:1 |
| Response Time (ms) (*1) | 8 |

Video Specs

| | |
|---------------------|---|
| Wide Mode | Auto / Wide Zoom / Normal / Full / Zoom |
| 4:3 Default | Yes |
| Video Processing | 4K X-Reality PRO |
| Motionflow | X-Motion Clarity, Auto mode |
| Compatible with HDR | Yes (HDR10, HLG, Dolby Vision) |
| | 4096 x 2160p (24,50,60Hz), 3840 x |

| | |
|--------------|---|
| Video Signal | 2160p (24,25,30,50,60Hz), 1080p (30,50,60,100,120Hz), 1080/24p, 1080i (50,60Hz), 720p (30,50,60Hz), 720/24p, 576p, 480p |
|--------------|---|

Audio Specs

| | |
|--------------------|-------------------------|
| Speaker Position | Side Back + Down Firing |
| Audio Power Output | 10W + 10W |

Network Specs

| | |
|-----------------------------|--|
| Wi-Fi direct | Yes |
| Wi-Fi Certified | Yes |
| DLNA | Home Network Client, Home Network Renderer |
| Miracast (screen mirroring) | Yes (only for B2B purpose) |
| Firmware Update | Yes |
| Wireless LAN | Integrated |

Convenience Features

MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS

| | |
|---------------------|---|
| USB Play (contents) | (HDV,AVCHD):MPEG2,AVC / MP4 (XAVCS):AVC,MPEG4,HEVC / AVI:Xvid,MotionJpeg / ASF (WMV):VC1 / MOV:AVC,MPEG4,MotionJpeg / MKV:Xvid,AVC,MPEG4,VP8.HEVC / WEBM:VP8 / 3GPP:MPEG4,AVC / MP3 / ASF (WMA) / LPCM / WAV / MP4AAC / FLAC / JPEG |
|---------------------|---|

| | |
|-----------------|-----|
| On Screen Clock | Yes |
|-----------------|-----|

| | |
|-------------|-----|
| Sleep Timer | Yes |
|-------------|-----|

| | |
|--------------|-----|
| On/Off Timer | Yes |
|--------------|-----|

| | |
|---------------------|-----|
| Chromecast Built-in | Yes |
|---------------------|-----|

| | |
|---------------|-----|
| Apple AirPlay | Yes |
|---------------|-----|

Inputs and Outputs

| | |
|------|-----------------------------------|
| HDCP | HDCP 2.3 (for HDMI 1 / 2 / 3 / 4) |
|------|-----------------------------------|

| | |
|--------------------------|----------|
| Composite Video Input(s) | 1 (Side) |
|--------------------------|----------|

| | |
|-----------------------------|------------|
| HDMI™ Connection(s) (Total) | 4 (4 Side) |
|-----------------------------|------------|

| | |
|-------------------------------|----------|
| Analog Audio Input(s) (Total) | 1 (Side) |
|-------------------------------|----------|

| | |
|-------------------------|----------|
| Digital Audio Output(s) | 1 (Side) |
| USB | 2 (Side) |
| Ethernet Connection(s) | 1 (Side) |

Design Features

| | |
|-------------------------------|------------------------------|
| Bezel Color | Black |
| Table Top Stand | Separate (assembly required) |
| VESA® Hole Spacing Compatible | Yes |
| VESA® Hole Pitch | 300 mm x 300 mm |

Eco and Energy Saving

| | |
|--------------------------------------|--|
| Screen Size (measured diagonally) | 75" (74.5") |
| Power Consumption (Rated / Standard) | 277W |
| Power Consumption (in Standby) | [Jordan or UAE or Egypt]:0.50W, [Other]:0.5W |
| Peak Luminance Ratio | TBD |
| Lead content | Yes |

| | |
|---|--|
| Mercury content (mg) | 0,0 |
| Power Requirements | AC110V for Taiwan, AC220-240V for Others |
| Power Saving Mode / Back Light Off Mode | Yes |
| Dynamic Backlight Control | Yes |
| Light Sensor | Yes |
| AC Power Input | C8 INLET (REAR) |

Regulatory approvals

| | |
|----------------------|------|
| Regulatory approvals | BSMI |
| *2 | RCM |

Measurements

| | |
|--|----------------------|
| Display Only (W x H x D) (Approx.) | 1674 x 961 x 71 mm |
| Display with Stand (W x H x D) (Approx.) | 1674 x 1031 x 410 mm |
| Package Carton (W x H x D) (Approx.) | 1812 x 1110 x 188 mm |

Weight

| | |
|--------------|---------|
| Display Only | 32.9 kg |
|--------------|---------|

| | |
|--------------------|---------|
| Display with Stand | 34.4 kg |
|--------------------|---------|

| | |
|----------------|-------|
| Package Carton | 46 kg |
|----------------|-------|

Display Specifications

| | |
|-------------------------------|--------------------|
| Viewing angle (Right/Left) | 178 (89/89) degree |
|-------------------------------|--------------------|

| | |
|----------------------------|--------------------|
| Viewing angle (Up/Down) | 178 (89/89) degree |
|----------------------------|--------------------|

| | |
|--------------------|------|
| Display Resolution | QFHD |
|--------------------|------|

| | |
|--------------|------|
| Aspect Ratio | 16:9 |
|--------------|------|

| | |
|----|-----------------|
| OS | Android 9.0 Pie |
|----|-----------------|

Signage Specs

| | |
|--------------------------------|-----|
| Easy HTML5 Signage Embedded | Yes |
|--------------------------------|-----|

| | |
|------------------|-----|
| Multicast / IPTV | Yes |
|------------------|-----|

Control Specs

| | |
|-----------------|----------|
| RS-232C Control | 1 (Side) |
|-----------------|----------|

| | |
|----------|-----|
| Pro Mode | Yes |
|----------|-----|

| | |
|------------|-----|
| IP Control | Yes |
|------------|-----|

| | |
|-------------------|-----|
| HDMI Auto Wake-up | Yes |
|-------------------|-----|

Notes

| | |
|----|--|
| *1 | Typical value of the panel specification |
|----|--|

| | |
|----|---|
| *2 | The information on this page is current as of the date of publication. Please contact your local office for the latest information. |
|----|---|

Further Information

Product

Information Sheet <https://eprel.ec.europa.eu/screen/product/electronic>

Gallery



