

## NXLK-IP45F

AV Multiplexer/Demultiplexer Board



**NETWORKED LIVE**

### Overview

#### **Ideal for handling audio and video signals in IP-based live production environment**

The NXLK-IP45F AV Multiplexer/Demultiplexer Board is capable of multiplexing or demultiplexing audio and video over IP. The board separates audio over IP and video over IP signals from video over IP or SDI inputs, or combines both into an SDI with embedded audio signal.

#### **Interconnects SDI-based equipment with IP-based infrastructure**

Option board for the NXL-FR318 Signal Processing Unit

#### **Video and audio format flexibility**

The board provides support for Dante audio over IP format and can handle both HD and 4K video formats.

### Features

#### **Audio over IP and video over IP multiplexer**

The NXLK-IP45F multiplexes audio over IP and video over IP signals and outputs an SDI signal with embedded audio.

#### **Audio over IP and video over IP demultiplexer**

The board demultiplexes audio from video over IP or an SDI signal with embedded audio and outputs separate audio over IP and video over IP signals.

## SDI to IP conversion

The board is capable of converting SDI to IP under demultiplexer mode.

## Supports major audio over IP format

The board provides support for Dante audio over IP format.

## Supports HD/4K

The board can handle both HD and 4K video formats.

## Specifications

### General specifications

Power supply	DC 12 V (supplied from NXL-FR318)
Power consumption	2.5 A 30 W (3 slot occupancy)
Dimensions	Main board: 114.5 × 28 × 275.8 mm (4 5/8 × 1 1/8 × 10 7/8 in.) (W × H × D) Connector board: 131 × 35.2 × 117.25 mm (5 1/4 × 1 7/16 × 4 5/8 in.) (W × H × D)
Mass	Main board: Approx. 244 g (8.6 oz)
Connector board	Approx. 250 g (8.8 oz)
Temperature ranges	Operation guaranteed temperature: 5 °C to 40 °C (41 °F to 104 °F) Performance guaranteed temperature: 10 °C to 35 °C (50 °F)

to 95 °F)  
 Storage temperature: -20 °C to +60 °C (-4 °F to +140 °F)

## I/O specifications

Connector	BNC type 75 Ω
-----------	---------------

Number of lines	Input/output: 4 Output: 4
-----------------	------------------------------

Signal formats	SMPTE ST 424
----------------	--------------

Connector	SFP+
-----------	------

Number of lines	2
-----------------	---

Signal formats	10GBASE-** (dependent on SFP+ transceiver module) For details on supported SFP+ transceiver modules (e.g., OTM-10GSR1), contact your local Sony service representative.
----------------	--

Connector	RJ-45
-----------	-------

Number of lines	2
-----------------	---

Signal formats	1000BASE-T
----------------	------------

## Supplied accessories

\*

Operation manual (1)

## Supported formats

SDI input/output

3840 x 2160 59.94p Level-A, 2SI or SQD, LLVC compression

3840 x 2160 50p Level-A, 2SI or SQD, LLVC compression

## Related products



NETWORKED LIVE

### PWS-110NM1

IP Live System Manager Station



NETWORKED LIVE

### OTM-10GSR1

10GBASE-SR SFP+ Transceiver for Sony Networked Media Interface products



NETWORKED LIVE

### NXL-FR316

SDI-IP signal processing unit



NETWORKED LIVE

### NXLK-IP40F

SDI-IP converter board with 3G-SDI and SFP+ ports



### BPU-4800

4K / HD baseband processor unit and UHFR server for HDC-4800 system camera

## Gallery

