

## UNI-ORL7T2W

Wireless-ready vandal resistant dome housing



### Overview

#### **Tinted bubble wireless-ready vandal resistant dome housing**

The Sony 7-inch Wireless-Ready Vandal-Resistant Outdoor Housing (Tinted Bubble) is designed to offer extra protection to the SNC series Dome Cameras. Made of durable engineered plastic, the top body of the housing is flame retardant and UV protected, making it an excellent choice for installation in outdoor and high-risk locations. Designed for discreet surveillance, the housing is equipped with a tinted lower dome that helps conceal the direction of the camera without interfering with the camera's view. A pre-run wireless antenna cable in the housing, when used with a compatible wireless card and antenna (sold separately), extends the wireless range of the network camera, while also allowing you to transmit videos over a mile. An integrated heater and blower system shields the camera in low temperatures and prevents the lower bubble from fogging up in high humidity.

#### **Rugged vandal-resistant long-lasting construction**

Upper body of the 7-inch (177.8 mm) housing is made of plastic and is 94 VO flame-rated. Dome shell is constructed of an injection moulded 0.118" (3 mm) thick, optically tinted thermoplastic polycarbonate. Strong cast aluminium top and trim ring.

## Features

### **Extreme temperatures**

Equipped with 24 VAC input blowers and thermostatically controlled heaters. 24-hour fan operation for effective heating and condensation protection.

### **Wireless ready**

Includes a pre-run wireless antenna cable that works with the SNCA-CFW1 or the SNCA-CFW5 wireless card and SNCA-AN1 antenna (sold separately) 2' (0.60 m) cable with N-type connector is included on top of enclosure for connecting an external antenna.

### **Power**

24 VAC input into enclosure supplies power to both the camera and housing.

### **Compatibility**

Designed for the SNC-RS44/46, SNC-RH124, SNC-RZ25, SNC-RX, SNC-ER/EP, and SNC-ZR/ZP outdoor dome cameras. 5.5" NPT quick connect coupling.

## Gallery

