

BRBK-SF1

HD optical multiplex card for
BRC-H900P and BRC-Z330
robotic cameras



Overview

Allows transmission of HD signal up to 2,000 metres with BRU-SF10 HD optical multiplex unit

The BRBK-SF1 interface card is designed for use for use with the BRC-H900P Full-HD robotic camera and the BRC-Z330 HD robotic camera. The combined use of this card, CCFC-S200200m single-mode optical fibre cable segments and BRU-SF10 HD optical multiplex unit allows up to 2,000 metres (6,562 feet) transmission of camera images, external video syncsignals, 2 analogue audio channels and control signals via optical fibre cable.

Related products



BRU-SF10

HD/SD Optical Multiplex Unit for BRC-H900 and BRC-Z330 cameras



BRC-Z330

1/3-inch CMOS sensor SD / HD robotic camera

Gallery

