

## MDR-7505

Compact professional headphones



### Overview

#### **For those who listen for a living**

The MDR-7505 provide a practical solution for high quality headphone monitoring in noisy environments.

**Sony professional headphones are engineered for daily use in broadcast and recording studios**

**Designed using the highest grade materials**

**All models fold to a convenient compact size**

### Features

#### **Gold plated Unimatch Plug**

Plug contains 3.5 mm and 6.3 mm adaptor

#### **Convenient folding design**

The Circum-aural design offers excellent isolation, making it ideal for outside broadcast, studio & DJ applications.

#### **High Quality Monitoring**

Neodymium magnet for powerful bass & clear treble

### Specifications

#### Generic Specifications

Power (mW): 1000

---

Impedance (Ohm): 24

---

Sensitivity (dB / W / m): 106

---

Frequency Response: 10Hz - 25kHz

---

Driver Diameter (mm): 50

---

Mass (g) (excluding cable): 220

---

## Supplied Accessories

1 x 3m coiled cable

---

## Gallery

