

MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



Specifications

General	
Type	Closed dynamic
Driver Unit	40 mm (1.58 in)
Power Handling Capacity	1,500 mW (IEC *1)
Impedance	50 Ω at 1kHz
Sensitivity	102 dB/mW
Frequency Response	5 Hz - 80,000 Hz (JEITA)
Mass	Approx. 216 g (without cable)
Included Items	Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide

Notes

*1

IEC International Electrotechnical
Commission

Related products



MDR-MV1

Open back Studio
Monitor Headphones
for creating spatial
and stereo sound
with wide frequency
range and soundstage
feel



MDR-7506

Stereo professional
headphones

Gallery

