

PSS-650

Projector Ceiling Bracket for Installation



Overview

Projector Ceiling Bracket for Installation

Specifications

Adjustable range

| | |
|------------------------------|---|
| Up/down position | 300~375mm / 11 13/16~14 3/4 inches 475~625 mm / 18 11/16~24 19/32 inches (with Supplied extension pole) (25mm pitch adjustment) |
| Horizontal angle of rotation | ± 10 deg |
| Left/right tilt angle | ± 5 deg (Fine adjustment function with adjustment knob) |
| Up/down tilt angle | ± 5 deg (Fine adjustment function with adjustment knob) |
| Front/back position | ± 50 mm / ± 1 31/32 inches (Fine adjustment function with adjustment knob) |
| Left/right position | ± 25 mm / ± 31/32 inch (Fine adjustment function with adjustment knob) |

Dimensions (W x H x D)

| | |
|------------------------|--|
| Dimensions (W x H x D) | 299 x Height* x 453.5 mm / 11 25/32 x H x 17 27/32 inches *Height: 300~375mm / 11 13/16~14 3/4 inches 475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole) |
|------------------------|--|

Dimensions (W x H x D) *without protrusions (Adjustment knob)

| | |
|---|--|
| Dimensions (W x H x D) *without protrusions (Adjustment knob) | 246 x Height* x 322 mm / 9 11/16 x H x 12 11/16 inches *Height : 300~375mm / 11 13/16~14 3/4 inches 475~625mm / 18 11/16~24 19/32 inches (with Supplied extension pole) |
|---|--|

