

BPU-4000

4K base band processor unit



Overview

Routes 4K signals from the PMW-F55 camera fitted with CA4000 4K fibre transmission adaptor

The BPU4000 works with the CA4000 to route 4K signals from the PMW-F55 Super 35mm 4K CMOS sensor camera. The BPU4000 generates 4K and HD signals at a similar colour matrix to match to the current Sony HD camera system, 4K and HD signal outputs simultaneously. The BPU4000 works with the HDCU-2000/2500 to permit the same system operation as the current HDC camera system.

4K migration path for HDC Series camera customers

The BPU4000 works with the same range of Remote Control Panels (RCPs) and Master Setup Units (MSUs) as current HDC Series system cameras, providing a future-proofed migration path for customers. The system works across standard SMPTE fibre cables for distances up to 2,000m.

This product contains pre-installed software and requires the purchase of licence keys to activate some functions.

Features

Routes 4K signals from the PMW-F55 camera fitted with CA4000

The BPU4000 works with the CA4000 to route 4K signals from the PMW-F55 Super 35mm 4K CMOS sensor camera. The BPU4000 generates 4K and HD signals at a similar colour matrix to match to the current Sony HD camera system, 4K and HD signal outputs simultaneously.

Supports HDCU-2000/2500 CCU operation

The BPU4000 works with the HDCU-2000/2500 to permit the same system operation as the current HDC camera system including Reference signal, Return Video signal, Tally, Intercom and Sony RCPs/MSUs.

4K fibre transmission up to 2,000m

The 4K Live system works across standard SMPTE fibre cables for distances up to 2,000m.

High Frame Rate recordings (Optional software)

The camera allows High frame rate (HFR) recordings up to 200 frames per second at 1080/50p

HD cut-out functionality (Optional software)

It is possible to cut out a Full HD image from the 4K picture in real-time, allowing, for example, for the camera to be in a fixed camera position and operator free giving a

wide view of the action, an area of which can be selected by the director.

Can operate without HDCU-2000/25000 CCU

The BPU4000 works without the HDC-2000/25000 CCU by supplying power to the PMW-F55 and CA4000 side locally. The BPU4000 has Reference signal and Return signal inputs and supports RCP control.

Related products



PWS-4400
4K / HD multi-port AV storage unit



HDCU-3100
IP enabled next generation Camera Control Unit



HDC-P43
4K/HD POV Camera



LA-FZB2
Lens mount adaptor from B4 mount to FZ mount



CA-4000
4K fibre transmission camera adaptor



PMW-F55
Super 35mm 4K CMOS sensor compact CineAlta camera records HD/2K/4K on SxS memory plus 16-bit RAW 2K/4K output



SZC-4002 / SZC-4002M / SZC-4002W
HFR Upgrade for F65, F55 and HDC-4300



HDC-4300
4K/HD System Camera



SZC-4001 / SZC-4001M / SZC-4001W
4K Upgrade for HDC-4300



SZC-2001 / SZC-2001M / SZC-2001W
HD Cut-Out Upgrade for BPU Series products



HDRC-4000
HDR Production Converter Unit



HKCU-SM100
CCU extension adaptor

Gallery

