

# OTM-100GSR

SFP28 Optical Transceiver Module (SR)



## Overview

**The OTM-100GSR is a QSFP28 Ethernet transceiver that supports 100GBASE-SR4**

## Specifications

### General specifications

Connector	LC Duplex optical connector
Signal Format	25GBASE-SR
Media Type	Multi Mode
Power requirements	3.3 V DC
Power consumption	3.5 W
External dimensions (width / height / depth)	18.35 × 12.9 × 122.3 mm (3/4 × 17/32 × 4 7/8 in)
Mass	36.81 g (1.3 oz) (max)
Temperature ranges	Operating temperature: 5 °C to 40 °C (41 °F to 104 °F) Storage temperature: -20 °C to +60 °C (-4 °F to +140 °F)

### I/O specifications

Optical input/output connectors	MPO optical connector
Signal format	802.3bm 100GBASE-SR4
Signal transmission speed	25.78125 Gbps per lane
Media type	Multi mode
Host interface	Connector: Card edge connector Signal format: SFF Committee SFF-8472 Specifications

## Related products



### **XVS-7000**

Mid-range 4K/3G/HD video switcher for IP and SDI



### **XVS-8000**

High-end 4K/3G/HD video switcher for IP and SDI



### **PWS-110NM1**

IP Live System Manager workstation



### **XVS-9000**

4K / 3G / HD multi-format IP-ready video switcher

## Gallery

