

Compact 720p/30 fps Camera - X Series



Overview

Features

Compact and Stylish design

DEPA

EXMOR® and CMOS Sensor®

Power over Ethernet (PoE) capability

ONVIF (Open Network Video Interface Forum) compliance

HD (720p) resolution

Supports multiple industry standard codecs: H264, MPEG-4 and JPEG with dual streaming capability

Stream Squared Function

Electronic Day/Night

Analogue Monitor Output

Specifications

This table is currently empty, consisting of a blue header bar at the top, a blue footer bar at the bottom, and a central area with 24 horizontal lines representing rows.

A series of horizontal lines forming a table structure. The table is divided into three main sections by three thick teal horizontal bars. Each section contains multiple rows of lines, suggesting a grid for data entry or specifications. The teal bars are positioned at approximately the 30%, 66%, and 92% vertical marks of the page.



Gallery





