

## MSU-3500

Master setup unit, multi camera remote control panel for system cameras (vertical type)



### Overview

**The MSU-3500 master setup unit allows intuitive control and maintenance for the connected Sony HDC series system cameras.**

Sharing the same compact vertical form factor and familiar ergonomics as the MSU-1500, the MSU-3500 fits a 9.5-inch EIA rack (half rack mount size). It can control multiple camera systems via either 1000Base-T LAN, or a single camera by direct peer-to-peer connection via Sony CCA cable.

Operability is enhanced via a new touchpanel with improved visibility plus additional LED indicators and assignable keys. The menu page gives direct access to camera, CCU and BPU functions for greater usability and expandability.

### Features

#### **Flexible, scalable system configuration**

The MSU-3500 can be configured for use with large and small-scale camera control systems, sharing the same mechanical dimensions and interface system as the MSU-1500 model. A MSU-3500 can flexibly control up to 96 units of HDC Series system camera.

#### **Customizable Switches**

Functions and Menu can be mapped to the assignable keys via the Menu Control page, allowing quick and easy access. There are 3 assignable keys on the panel. This is available via SW Customize menu with the categorized items.

#### **USB flash drive**

The MSU's settings can be saved or loaded via USB flash drive. CAM/CCU/BPU Scene files/Reference files can also be saved, and for the HDRC-4000's HDR Production Converter Unit the All Setting file can be saved.

#### **New LCD touchpanel**

The large LCD touchpanel features a new 7-inch WVGA (800x480) panel with improved visibility.

#### **High speed LAN connection**

The MSU-3500 supports connectivity via 1000Base-T Ethernet LAN in addition to a single connection by Sony CCA 8-pin cable.

#### **Web UI application**

Allows convenient remote operation for MSU initial settings from a remote networked PC with intuitive user interface (UI).\*

\* Feature available at later date.

#### **Status indication**

By the Status key, the connected camera/CCU/BPU's alert status can be indicated on the LCD panel if it occurs. Some of the setting status can be also indicated.

## General

Power Supply	AC 100 - 240 V 50/60 Hz 0.30 A (Max.) DC 10.5 - 17 V 2.3 A (Max.)
Operating Temperature	5 °C to 40 °C (41 °F to 104 °F)
Storage Temperature	-20 °C to 60 °C (-4 °F to 140 °F)
Dimensions (W x H x D)	204 x 310 x 67 mm (8 1/8 x 12 1/4 x 2 3/4 inch) (excluding protrusions)
Mass	Approx. 3.4 kg (7 lb. 8 oz.)

## Input/output Connectors

LAN	RJ-45 8pin (x1) 1000BASE-T, 100BASE-TX, 10BASE-T
Remote CCU/CNU	Multi-connector 8-pin, female (x1)
AUX	Multi-connector 8-pin, female (x1)
I/O Port	D-Sub 50-pin, female (x1)
AC In	3-pin (x1)
DC In	XLR 4-pin (x1)

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.

# Related products



## MSU-3000

Master setup unit, multi camera remote control panel for system cameras (horizontal type)



## RCP-1000

Joystick type of simple Remote Control Panel for HDC/HSC/HXC series cameras. 6 units in 19-inch EIA rack.



## RCP-1001

Dial type of simple Remote Control Panel for HDC/HSC/HXC series cameras. 6 units in 19-inch EIA rack.



## MSU-1000

Master setup unit, multi camera remote control panel for HDC / HSC cameras (horizontal type)



## MSU-1500

Master setup unit, multi camera remote control panel for HDC / HSC cameras (vertical type)



## RCP-1500

Joystick type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



## RCP-1501

Dial type of Remote Control Panel for HDC/HSC/HXC series cameras. 4 units in 19-inch EIA rack.



## RCP-1530

Joystick type of Remote control panel for HDC/HSC/HXC series cameras. 5 units in 19-inch EIA rack.



## CNA-1

Camera control network adaptor



## HDC-P31

2/3-type 3-CMOS sensor POV system camera



## UHC-8300

1.25-type 8K 3-CMOS sensor portable system camera with 8K 2x HFR capability



## HDCU-3100

IP enabled next generation Camera Control Unit



## HDCU-3170

IP capable Triax Camera Control Unit



## HDCU-3500

IP-ready Camera Control Unit (CCU) for HDC-3500 4K/HD system camera



## HDCU-5000

Camera Control Unit (CCU) for HDC-5500 and HDC-3500/3100 series system cameras



## HDCU-5500

IP-ready Camera Control Unit (CCU) for HDC-5500 4K/HD system camera



## HDC-P50

2/3-type 4K 3-CMOS sensor POV system camera with HD 6x HFR capability



## HXCU-FB80

4K / HD Camera Control Unit for HXC-FB80 cameras



## HXC-P70

Affordable, three 2/3-inch Exmor CMOS sensor, full HD/SD compact system camera with direct optical fibre cable connection



## BRC-X1000

Premium 4K30P PTZ Camera with 12x optical zoom and uncompromising broadcast picture quality



## BRC-X400

Premium 4K30P IP PTZ Camera with 30x (w/CIZ) zoom and NDI® | HX capability for use in a wide range of environments



## BRC-H800

Premium Full HD PTZ Camera with 12x optical zoom and uncompromising broadcast picture quality



## RCP-3500

Remote-control panel for HDC/HSC/HXC series cameras



## RCP-3501

Remote-control panel for HDC/HSC/HXC series cameras



---

© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.