

VPL-EX575

4,200 lumens XGA high brightness compact projector



Overview

Present clear, bright images, with flexible connectivity and low running costs

The VPL-EX575 projector is ideal for mid-sized classrooms and meeting rooms.

Quiet, compact and powerful, it delivers XGA images with 4,200 lumens colour light output and high 20,000:1 contrast ratio that can be seen clearly even in bright rooms and with larger projection screens, with Sony's 3LCD technology assuring natural, vivid colours. Image quality is further improved compared with previous models, with a new colour/white balance setting for crisp reproduction of on-screen text and a new 'Vivid' picture mode ensuring even richer, more vibrant colours.

The VPL-EX575 is an ideal partner for today's integrated AV/IT environments, expanding your connectivity options with dual HDMI ports and Direct USB Display connection. A convenient input label function makes life simpler, confirming on screen the name of connected devices.

Add the VPL-EX575 to a network and see presentations from up to four connected PC/Mac computers simultaneously. Slip in an optional Wi-Fi dongle and present directly wirelessly from laptops.

A range of energy-saving features plus up to 10,000 hours recommended lamp replacement time contribute to low ownership costs. Routine maintenance is quick and easy with a convenient rear lamp access feature.

Features

Bright, clear images with maximum 4,200 lumens colour light output

With a 4,200 lumen maximum light output (in high mode), the VPL-EX575 delivers crisp, high-contrast presentations that can be seen clearly in bright rooms or on larger screens. There's a choice of three brightness modes to suit any environment, from bright daylight to darkened rooms.

3LCD BrightEra™ technology

The efficient 3LCD panel system is enhanced by advanced BrightEra™ technology for impressively bright, consistent, high resolution images with excellent colour accuracy and impressive reliability.

XGA resolution

XGA (1024 x 768) 4:3 display resolution gives plenty of crisp detail: ideal for making presentations direct from a laptop, mobile device or DVD player.

Powerful 16W audio

The powerful built-in 16W speaker (mono) lets your audience hear video soundtracks with no need for additional amplification.

Energy efficient with long-lasting lamp life up to 10,000 hours

High-performance lamp technology offers reduced ownership costs plus reduced maintenance, with a recommended lamp replacement time of approx. 10,000 hours (with brightness in low mode - may vary depending on environment or how the projector is used).

Advanced energy-saving features

Advanced lamp technology enables a range of energy-saving features. Auto Light Dimming mode saves energy when the projector is left on without being used. Auto Picture Mode automatically adjusts light output to suit the projected scene. Touching a button on the remote mutes the picture temporarily, dramatically reducing power consumption.

Quiet operation

Near-silent projector fan ensures discreet, unobtrusive operation in classrooms and meeting rooms.

Lamp Mode : High 35dB / Standard 33dB / Low 29dB

Auto power on

Save time and start presenting faster: the projector automatically turns on when signals are detected from a connected PC.

Quick go

Don't waste time when you're in a hurry to leave the room: turn off the projector and unplug immediately, with no lengthy waiting for cool-down.

Networked and wireless presentations

Project presentations from PC or Mac via network and wireless. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. The Projector Station for Network Presentation application for Windows/Mac is included.

Control and management from any networked PC

Projector functions and status can be managed and monitored remotely from any networked PC, using the included Projector Station for Network Control application.

Remote Control app for iOS/Android

Download the free Projector Remote app and control the projector from anywhere in the room with your handheld device, with simple easy-to-read buttons on your phone or tablet screen.

USB media viewer

Slip in a USB drive and display photos, images and graphics with no PC needed.

Dual HDMI inputs

Two HDMI input terminals make it easy to connect HDMI-equipped devices like PCs and media streaming devices.

IP control sync for easy system expansion

Control signals (power on/off, input select) from a master projector can be distributed over an IP network to additional 'sub' projectors.

USB Display function for easy one-cable PC connection

Present pictures and audio* from a connected PC or Mac with a single USB cable - you don't even need to install a software driver.

* There may be a time lag between video and audio. For low-latency applications it is recommended to use projector's line-in or HDMI-in connection.

Customised input naming labels

Define your own input labels like 'BD Player', 'PC' and 'Document Camera', making it easier to see on screen what devices are connected and being used.

Easy maintenance

Convenient lamp access at the rear of the projector body makes lamp swaps simpler when the projector is hanging from a ceiling mount.

Specifications

Display System

| | |
|----------------|--------------|
| Display System | 3 LCD system |
|----------------|--------------|

Display device

| | |
|--------------------------------|---|
| Size of effective display area | 0.63" (16mm) x 3 BrightEra LCD Panel Aspect ratio 4:3 |
|--------------------------------|---|

| | |
|------------------|---------------------------------|
| Number of pixels | 2,359,296 (1024x768 x 3) pixels |
|------------------|---------------------------------|

Projection lens

| | |
|-------|--------|
| Focus | Manual |
|-------|--------|

| | |
|---------------------|--------|
| Zoom Powered/Manual | Manual |
|---------------------|--------|

| | |
|--------------|---------------|
| Zoom - Ratio | Approx. x 1.6 |
|--------------|---------------|

| | |
|-------------|------------------|
| Throw Ratio | 1.40:1 to 2.27:1 |
|-------------|------------------|

Light source

| | |
|------|----------------------------------|
| Type | Ultra high pressure mercury lamp |
|------|----------------------------------|

| | |
|---------|------------|
| Wattage | 225 W type |
|---------|------------|

Recommended lamp replacement time *3

| | |
|-----------------|--------|
| Lamp mode: High | 4000 H |
|-----------------|--------|

| | |
|---------------------|--------|
| Lamp mode: Standard | 6000 H |
|---------------------|--------|

| | |
|----------------|---------|
| Lamp mode: Low | 10000 H |
|----------------|---------|

Filter cleaning / replacement cycle (Max.)

| | |
|--|---------|
| Filter cleaning / replacement cycle (Max.) | 10,000H |
|--|---------|

Screen size

| | |
|-------------|--|
| Screen size | 30" to 300" (0.76 m to 7.62 m) (measured diagonally) |
|-------------|--|

Light output *1

| | |
|-----------------|---------|
| Lamp mode: High | 4200 lm |
|-----------------|---------|

| | |
|---------------------|---------|
| Lamp mode: Standard | 3000 lm |
|---------------------|---------|

Light output *1

| | |
|----------------|---------|
| Lamp mode: Low | 2300 lm |
|----------------|---------|

Color light output *1

| | |
|-----------------|---------|
| Lamp mode: High | 4200 lm |
|-----------------|---------|

| | |
|---------------------|---------|
| Lamp mode: Standard | 3000 lm |
|---------------------|---------|

| | |
|----------------|---------|
| Lamp mode: Low | 2300 lm |
|----------------|---------|

Contrast ratio (full white / full black) *2

| | |
|---|---------|
| Contrast ratio (full white / full black) *2 | 20000:1 |
|---|---------|

Speaker

| | |
|---------|-------------------------|
| Speaker | Speaker 16 W (monaural) |
|---------|-------------------------|

Displayable scanning frequency

| | |
|------------|------------------|
| Horizontal | 15 kHz to 92 kHz |
|------------|------------------|

| | |
|----------|----------------|
| Vertical | 48 Hz to 92 Hz |
|----------|----------------|

Display resolution

| | |
|-----------------------|---|
| Computer signal input | Maximum display resolution: 1600 x 1200 dots, fV:60Hz |
|-----------------------|---|

| | |
|--------------------|--|
| Video signal input | NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, 1080/50p |
|--------------------|--|

Colour system

| | |
|---------------|---|
| Colour system | NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N, PAL60 |
|---------------|---|

Keystone Correction (Max) *4

| | |
|----------|---------------|
| Vertical | +/-30 degrees |
|----------|---------------|

OSD languages

| | |
|---------------|--|
| OSD languages | 27-languages (English, French, German, Italian, Spanish, Portuguese, Japanese, Simplified Chinese, Traditional Chinese, Korean, Russian, Dutch, Norwegian, Swedish, Thai, Arabic ,Turkish, Polish, Vietnamese, Farsi, Finnish, Indonesian, Hungary, Greek, Czech, Slovakia, Romania) |
|---------------|--|

INPUT OUTPUT (Computer/Video/Control)

| | |
|---------------|---|
| INPUT A | RGB / Y PB PR inputconnector: Mini D-sub 15 pin female Audio input connector: Stereo mini jack |
| INPUT B | RGB input connector: Mini Dsub 15 pin female Audio input connector: Stereo mini jack |
| INPUT C | HDMI input connector: HDMI 19-pin, HDCP support Audio input connector: HDMI audio support |
| INPUT D | HDMI input connector: HDMI 19-pin, HDCP support Audio input connector: HDMI audio support |
| S VIDEO IN | S Video input connector: Mini DIN 4-pin |
| VIDEO IN | Video input connector: Phono jack |
| OUTPUT | MONITOR output connector: Mini D-sub 15 pin female Audio output connector: Stereo mini jack |
| REMOTE | D-sub 9-pin male/RS232C |
| LAN | RJ-45, 10BASE-T/100BASE-TX |
| USB | Type-A |
| USB | Type-B |
| MICROPHONE IN | Microphone jack: Mini Jack |

Acoustic Noise *5

| | |
|----------------|------|
| Lamp mode: Low | 29dB |
|----------------|------|

Operating temperature / Operating humidity

| | |
|---|---|
| Operating temperature / Operating humidity | 0°C to 40°C (32°F to 104°F) /20-80% (no condensation) |
|---|---|

Storage temperature / Storage humidity

Storage temperature /Storage humidity -10 °C to +60°C (14°F to +140°F) /20% to 80% (no condensation)

Power requirements

Power requirements AC 100 V to 240 V, 3.4 A to 1.5 A, 50 Hz / 60 Hz

Power consumption

AC 100 V to 120 V Lamp mode: High 333 W

AC 220 V to 240 V Lamp mode: High 320 W

Power Consumption (Standby Mode)

AC 100 V to 120 V 0.50 W (when "Standby mode" is set to "Low")

AC 220 V to 240 V 0.50 W (when "Standby mode" is set to "Low")

Power Consumption (Networked Standby Mode)

AC 100 V to 120 V 5.5W (LAN)
6.0W (optional WLAN module)
6.2W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

AC 220 V to 240 V 5.8W (LAN)
6.3W (optional WLAN module)
6.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")

Standby Mode Networked Standby Mode Activated

Standby Mode Networked Standby Mode Activated Approx. 10 Minutes

Wireless Network(s) On/Off Switch

Wireless Network(s) On/Off Switch

- 1) Press the MENU button, then select [Connection/Power]
- 2) [WLAN Settings]
- 3) [WLAN Connection]
- 4) Select On or Off

Heat dissipation

AC 100 V to 120 V 1136 BTU/h

Heat dissipation

| | |
|-------------------|------------|
| AC 220 V to 240 V | 1092 BTU/h |
|-------------------|------------|

Dimensions (W x H x D)

| | |
|---|---|
| Dimensions (W x H x D) (without protrusions) | Aprox. 365 x 96.2 x 252mm (14 3/8 x 3 25/32 x 9 29/32") |
|---|---|

Mass

| | |
|------|----------------------|
| Mass | Approx. 4kg (8.8 lb) |
|------|----------------------|

Supplied accessories

| | |
|------------------|--------|
| Remote commander | RM-PJ8 |
|------------------|--------|

Wireless LAN Module

| | |
|---------------|----------|
| Optional Lamp | LMP-E221 |
|---------------|----------|

| | |
|----------------------|----------|
| Optional Accessories | IFU-WLM3 |
|----------------------|----------|

Notes

| | |
|----|-------------------------|
| *1 | The values are estimate |
|----|-------------------------|

| | |
|----|--|
| *2 | This value is average with lamp dimming. |
|----|--|


| | |
|----|---|
| *3 | The figures are approximate. They vary depending on the environment or how the projector is used. |
|----|---|

| | |
|----|--|
| *4 | The picture quality may deteriorate when the V Keystone function is used for it is an electrical correction. |
|----|--|

| | |
|----|---|
| *5 | The figures are approximate. They vary depending on the environment or how the projector is used. |
|----|---|

| | |
|---|---|
| Environmental notice for customers in the USA | Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for additional information. |
|---|---|

Information on EU Data Act: [Click here](#) to check if your Sony product and/or related service is subject to the EU Data Act.



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.