

## BKM-250TG

### 3G/HD/SD-SDI Input Adaptor



#### Overview

The BKM-250TG 3G-SDI interface board is compliant with the SMPTE 425 standard and requires only one single SDI cable to transmit up to 10-bit 4:2:2 1080P/60P video signals. This optional 3G-SDI interface offers a simple cabling solution for groups of video equipment rack-mounted behind an editing room.

#### Specifications

##### Input

BNC (x2)

Input impedance: 75 ohms  
unbalanced

Sampling frequency

3G-SDI:

Y/Cb/Cr (4:2:2)

148.5 MHz/74.25 MHz/74.25 MHz

Y/Cb/Cr (4:4:4)

148.5 MHz/148.5 MHz/148.5 MHz

G/B/R

148.5 MHz/148.5 MHz/148.5 MHz

SDI Input

HD-SDI:

Y/Cb/Cr 74.25 MHz/37.125 MHz/37.125 MHz  
SD-SDI:  
Y/Cb/Cr:13.5 MHz/6.75 MHz/6.75 MHz  
Quantization  
3G-SDI: 10 bits/sample, 12 bits/sample  
HD-SDI: 10 bits/sample  
SD-SDI: 10 bits/sample

---

## Output

BNC (x2) (monitor output) \*1  
Output signal amplitude: 800 mVp-p  $\pm 10\%$   
Output impedance: 75 ohms unbalanced  
SDI Output  
Transmission distance  
3G-SDI: 70 m (approx.230 ft) max. \*2  
HD-SDI: 100 m (approx.328 ft) max. \*2  
SD-SDI: 200 m (approx.656 ft) max. \*3

---

## Timecode Display

Available Standard	SMPTE-12M-2
--------------------	-------------

Timecode Type	VITC, LTC
---------------	-----------

## Audio Level Meter Display

Channel	CH1 to CH8 or CH9 to CH16
---------	---------------------------

Level	-60 dB to -0.01dB
-------	-------------------

Color	-0.01 dB to 0 dB: Red -1.25 dB to -0.01 dB: Orange -20 dB to 1.25 dB: Yellow -60 dB to -20 dB: Green
-------	---

## General

Voltage	+3.3 V, +5 V DC (supplied from the main unit)
---------	---

Power Consumption	Approx. 4.0 W
-------------------	---------------

Operating Temperature	0°C to 35°C (Recommended: 20°C to 30°C) 32°F to 95°F (Recommended: 68°F to 86°F)
-----------------------	---

Operating Humidity	0% to 90% (no condensation)
--------------------	-----------------------------

Storage/Transport Temperature	-20°C to +60°C -4°F to +140°F
Storage/Transport Humidity	0% to 90%
Operating/Storage/Transport Pressure	700 hPa to 1060 hPa
Dimensions (W x H x D) *4	100 x 20 x 162 mm 4 x 13/16 x 6 1/2 inches
Mass	Approx. 270 g Approx. 9.5 oz
Supplied Accessories	Operating Instructions (1)

## Notes

Note	<p>*[1] The signal from the monitor output</p> <p>*[2] When using 5C-FB coaxial cables (Fujikura or equivalent).</p> <p>*[3] When using 5C-2V coaxial cables (Fujikura or equivalent).</p> <p>*[4] The values for dimensions are approximate.</p>
------	---

## Gallery



