

## BTA-801

### Portable Tuner Mount Adaptor



### Overview

- Allows a WRR-855A/855B to be mounted on a Sony professional camcorder
- Supplies DC power from a camcorder to the WRR-855A/855B via an incorporated DC/DC converter

### Specifications

#### Audio Section

Analog Output	XLR-3-11C type (x1)
---------------	---------------------

#### General

Power Requirements	DC 10 to 17 V (12 V nominal)
--------------------	------------------------------

Power Consumption	200 mA DC or less (at DC 7 V)
-------------------	-------------------------------

Operating Temperature	32°F to 122°F 0°C to 50°C
-----------------------	------------------------------

Storage/Transport Temperature	-4°F to +140°F -20°C to +60°C
-------------------------------	----------------------------------

Dimensions <sup>*[1]</sup>	<p>φ88 x 142.5 x 31.5 mm (W x H x D)  (including projecting parts)</p> <p>φ3 1/2 x 5 5/8 x 1 1/4 inches (W x H  x D) (including projecting parts)</p>
Mass	<p>Approx. 6.3</p> <p>Approx. 180 g</p>
Supplied Accessories	<p>Operating Instructions (1)</p> <p>DC power cable (1)</p> <p>Betacam attachment kit (1 set)</p> <p>-Holder (1)</p> <p>Bracket (1)</p> <p>Binding head screws (M4 x 6) (2)</p>

## Notes

Note	<p><sup>*[1]</sup> The values for dimensions are approximate.</p>
------	---

## Gallery

