

FWD-55A8G/T

55" BRAVIA 4K Ultra HD, HDR,
OLED Professional Display



Overview

Make an impressive statement with exquisite 4K HDR images, effortless style and sound to match

Add unprecedented impact to your visual communications with the stunningly styled, fully featured FWD-55A8G/T 55" BRAVIA OLED Professional Display. Combining bright, beautiful 4K HDR image quality with easy operation, flexible networking/control and extensive integration options, it's an imposing addition to corporate boardrooms, lobbies and reception areas.

Optimised for professional display applications, BRAVIA takes full advantage of cutting edge OLED display technologies and our power-packed X1™ Extreme processor to ensure vibrant high-contrast 4K images.

The beautifully sleek, minimalist design of the FWD-55A8G/T is sure to impress in any setting. And with Acoustic Surface Audio™, cinematic sound comes directly from the 55" screen.

With advanced control, Pro Mode, optional interactive compatibility and an embedded HTML5 platform, it makes it easy to create attractive digital signage so you always present a clear image.

Enrich your audience's display experience with seamless TEOS

integration and a choice of built-in solutions to add extra functionality, from meeting room support to automation, with no need for any external devices or players.

For even greater peace of mind there's the added reassurance of our 3 Year Advanced Exchange PrimeSupport service. If there's a problem with your display, we'll offer a free, brand new replacement product rather than repair included as standard. You can also choose to extend your service by 2 additional years.

Features

4K image resolution (3840 x 2160 pixels)

4K offers four times the detail of Full HD, with a resolution of over 8 million pixels bringing extra clarity to corporate display, education and digital signage applications.

High contrast OLED screen technology

Each self-illuminating pixel is precisely and individually controlled, for exquisite images with unprecedented contrast.

Spectacularly real 4K HDR images

The 4K HDR Processor X1™ Extreme includes powerful real-time image processing for exceptionally detailed, lifelike pictures. Lower resolution images are upscaled closer to true 4K HDR quality.

More colour with TRILUMINOS Display

TRILUMINOS Display maps colours from a wider palette, faithfully reproducing a world of richer, more lifelike hues and tones.

Smoother movement

Motionflow XR inserts additional picture frames between the originals, ensuring smoother, sharper detail in fast-moving sequences.

Optimised for professional use

The FWD-55A8G/T meets the needs of today's business and

educational environments, with flexible installation options plus wired or wireless network connection and serial communication control.

TEOS integration

BRAVIA integrates seamlessly with TEOS, Sony's suite of workspace management applications that orchestrate control of devices and content in boardrooms, meeting areas and public spaces.

Easily create digital signage

Integrated support for HTML5 makes it easy to produce compelling digital signage, with no extra hardware or prior training needed. Combine graphics, text, 4K video and live web content to create attractive signage in minutes.

Sound from the screen

With Acoustic Surface Audio™, sound comes directly from the screen. Two actuators behind the TV vibrate to create acoustics that move with the picture.

Do more with Android TV

Discover a world of apps and online content powered by Android TV. Use Voice Search to find content easily with no typing.

Quick set-up with Pro Mode

Customise and store display settings and features, then copy them easily to multiple displays via USB flash memory.

Greater peace of mind

There's extra reassurance with our 3 Year Advanced Exchange PrimeSupport service that's included as standard. If there's a fault with your BRAVIA Professional Display, we'll provide a replacement unit at no extra charge to keep you up and running.

Specifications

TV System

| | |
|---------------------------------|----------|
| TV System (Digital Terrestrial) | DVB-T/T2 |
|---------------------------------|----------|

| | |
|---------------------------|-------|
| TV System (Digital Cable) | DVB-C |
|---------------------------|-------|

| | |
|-------------------------|----------|
| TV System (Digital Sat) | DVB-S/S2 |
|-------------------------|----------|

| | |
|--------------------------------------|--------------------------|
| Number of Tuners (Terrestrial/Cable) | 2 (Digital) / 1 (Analog) |
|--------------------------------------|--------------------------|

| | |
|------------------------|---|
| Number of Tuners (Sat) | 2 |
|------------------------|---|

Display features

| | |
|----------------|------|
| Display device | OLED |
|----------------|------|

Video specs

| | |
|-----------|---|
| Wide Mode | Wide zoom / Normal / Full / Zoom / 14:9 |
|-----------|---|

| | |
|-------------|-----|
| 4:3 Default | Yes |
|-------------|-----|

| | |
|------------------|------------------|
| Video Processing | 4K X-Reality PRO |
|------------------|------------------|

| | |
|------------|---------------|
| Motionflow | Motionflow XR |
|------------|---------------|

| | |
|---------------------|--------------------------------|
| Compatible with HDR | Yes (HDR10, HLG, Dolby Vision) |
|---------------------|--------------------------------|

| | |
|--------------|--|
| Video Signal | 4096 x 2160p (24, 50, 60Hz), 3840 x 2160p (24, 25, 30, 50, 60Hz), 1080p (30, 50, 60Hz), 1080/24p, 1080i (50, 60Hz), 720p (30, 50, 60Hz), 720/24p, 576p, 576i, 480p, 480i |
|--------------|--|

Audio specs

| | |
|------------------|---------------------|
| Speaker position | Front + Down Firing |
|------------------|---------------------|

| | |
|--------------------|---------------------------|
| Audio Power Output | 10 W + 10 W + 10 W + 10 W |
|--------------------|---------------------------|

Network specs

| | |
|--------------|-----|
| Wi-Fi direct | Yes |
|--------------|-----|

| | |
|-----------------|-----|
| Wi-Fi Certified | Yes |
|-----------------|-----|

| | |
|------|--|
| DLNA | Home Network Client, Home Network Renderer |
|------|--|

| | |
|-----------------------------|-----|
| Miracast (screen mirroring) | Yes |
|-----------------------------|-----|

| | |
|-----------------|-----|
| Firmware update | Yes |
|-----------------|-----|

| | |
|------------------|------|
| Internet Browser | Vewd |
|------------------|------|

| | |
|--------------|------------|
| Wireless LAN | Integrated |
|--------------|------------|

Professional Features

| | |
|--|--|
| Professional Hidden Mode | Yes |
| HDMI auto wake-up | Yes |
| HTML platform | Yes |
| Multicast / IPTV | Yes |
| Compatible with TEOS Workplace Management Solution | Yes |
| Available storage | 16 GB |
| Compatible TEOS Content | Customised design, text, pictures, videos, YouTube, traffic, weather, public information, Facebook, Twitter, PowerPoint and more |

Convenience features

| | |
|---------------------|--|
| USB Play (contents) | MPEG1:MPEG1 / MPEG2PS:MPEG2 / MPEG2TS (HDV, AVCHD):MPEG2, AVC / MP4 (XAVC S):AVC, MPEG4, HEVC / AVI:Xvid, MotionJpeg / ASF (WMV):VC1 / MOV:AVC, MPEG4, MotionJpeg / MKV:Xvid, AVC, MPEG4, VP8. HEVC / WEBM:VP8 / |
|---------------------|--|

3GPP:MPEG4, AVC / MP3 / ASF
(WMA) / WAV / MP4AAC / FLAC /
JPEG

| | |
|-----------------|-----|
| On screen clock | Yes |
| Sleep timer | Yes |
| On/Off timer | Yes |
| Google Cast | Yes |

Inputs and outputs

| | |
|--------------------------------|---|
| HDCP | HDCP2.3 (for HDMI 1 / 2 / 3 / 4) |
| RF Connection Input(s) | 1 (Bottom) |
| Composite Video Input(s) | 1 (Side) |
| HDMI™ Connection(s) (Total) | 4 (1 Side, 3 Bottom) |
| Digital Audio Output(s) | 1 (Bottom) |
| Audio Out | 1 (Side / Hybrid with Headphone Out) |
| USB | 2 (Side) / 1 (Bottom) |

| | |
|------------------------|------------|
| Ethernet Connection(s) | 1 (Bottom) |
|------------------------|------------|

Design features

| | |
|------------------------|-------|
| Finish (Surface Color) | Black |
|------------------------|-------|

| | |
|-----------------|------------------------------|
| Table Top Stand | Separate (assembly required) |
|-----------------|------------------------------|

| | |
|-------------------------------|-----|
| VESA® Hole Spacing Compatible | Yes |
|-------------------------------|-----|

| | |
|------------------|----------------|
| VESA® Hole Pitch | 30.0 x 30.0 cm |
|------------------|----------------|

Eco and energy saving

| | |
|---------------------|---|
| Energy Label Rating | B |
|---------------------|---|

| | |
|-----------------------------------|-------------|
| Screen size (measured diagonally) | 55" (54.6") |
|-----------------------------------|-------------|

| | |
|-------------------|-----------------|
| Power Consumption | Standard: 130 W |
|-------------------|-----------------|

| | |
|--------------------------|--------------|
| Annual Power Consumption | 180 kWh/Year |
|--------------------------|--------------|

| | |
|--------------------------------|--------|
| Power Consumption (in Standby) | 0.50 W |
|--------------------------------|--------|

| | |
|--|--|
| Power Consumption (networked standby mode) | 2.00 W (Wi-Fi) / 2.00 W (LAN) / 0.50 W (CEC) |
|--|--|

| | |
|--|-------------|
| Peak Luminance Ratio | 73% |
| Lead content | Yes |
| Mercury content (mg) | 0.0 |
| Power Requirements | AC 220-240V |
| Power Saving Mode / Back Light Off Mode | Yes |
| Dynamic Backlight Control | Yes |
| Light Sensor | Yes |
| AC Power Input | 1 (REAR) |

Measurements

| | |
|---|---|
| Display Only (W x H x D) (Approx.) | Approx. 122.9 x 71.0 x 5.1 (0.64) cm |
| Display with Stand (W x H x D) (Approx.) | Approx. 122.9 (122.9) x 73.0 (78.0) x 29.0 (29.0) cm |
| Package Carton (W x H x D) (Approx.) | Approx. 141.1 x 83.6 x 18.5 cm |

Weight

| | |
|--------------|---------|
| Display Only | 17.6 kg |
|--------------|---------|

| | |
|--------------------|---------|
| Display with Stand | 19.8 kg |
|--------------------|---------|

| | |
|----------------|-------|
| Package Carton | 27 kg |
|----------------|-------|

Display specifications

| | |
|------------------------------|----------------------|
| Viewing angle (Right / Left) | 178 (89 / 89) degree |
|------------------------------|----------------------|

| | |
|---------------------------|----------------------|
| Viewing angle (Up / Down) | 178 (89 / 89) degree |
|---------------------------|----------------------|

| | |
|--------------------|------|
| Display resolution | QFHD |
|--------------------|------|

| | |
|--------------|------|
| Aspect ratio | 16:9 |
|--------------|------|

| | |
|----|--------------------|
| OS | Android 7.0 Nougat |
|----|--------------------|

Signage specs

| | |
|-----------------------------|-----|
| Easy HTML5 Signage embedded | Yes |
|-----------------------------|-----|

| | |
|------------------|-----|
| Multicast / IPTV | Yes |
|------------------|-----|

Control specs

| | |
|----------------|-----|
| Hotel Mode Pro | Yes |
|----------------|-----|

| | |
|------------|-----|
| IP Control | Yes |
|------------|-----|

HDMI auto wake-up Yes

PrimeSupport

Included
PrimeSupport

3 years of Standard helpdesk (Mon-Fri 9:00-18:00 CET) and Advanced Replacement service in case of product fault with all logistics covered.

Optional
PrimeSupport
Extensions

Optional 2-year support extension available: PSP.FWOL-55.2X

Gallery



