

ODBK-103

*Please contact your local sales representative for details.



Overview

Extension kit for the ODS-L30M

A world of solutions

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy, reliable access to your precious data is crucial – along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

Related products



ODS-L30M

*Please contact your local sales representative for details.



ODS-L60E

*Please contact your local sales representative for details.



ODS-L100E

*Please contact your local sales representative for details.



ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read

using ODC-3300R
Generation 2 cartridge



ODS-D77F

Optical Disc Archive
fibre channel drive
unit for ODS-L30M
PetaSite scalable
library with transfer
speeds up to 1,150
Mbps (read) and 780
Mbps (write-once
disc) or 310 Mbps
(rewritable disc)



ODS- D380F

*Please contact your
local sales
representative for
details.

Gallery

