

## SCA-S30



### Features

### Easy to install

### Related products



#### **SNC- VB635**

Box-type 1080p/60 fps Camera with Half-inch Exmor™ CMOS Sensor Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VB630**

Box-type 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VB600**

Box-type 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VM632R**

Outdoor IR Ruggedized 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VM602R**

Outdoor IR Ruggedized 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VM631**

Vandal-resistant Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VM630**

Minidome 1080p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



#### **SNC- VM601**

Vandal-resistant Minidome 720p/60 fps Camera Powered by IPELA ENGINE EX™ - V Series



## **SNC- VM600**

Minidome 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series

## Gallery

