

## SNC-DH110T

Compact 720p/30 fps Camera - X Series



### Overview

The SNC-DH110T is an indoor high definition (720p, supporting H.264 at 30fps) 1.3 Megapixel (1280 x 960 maximum resolution) vandal resistant compact minidome camera with Electronic Day/Night function, DEPA and ONVIF compliance. It supports dual streaming and triple codec encoding.

Sony's X-Series cameras have outstanding picture quality and a compact, affordable, stylish design.

### Features

#### **Compact and Stylish design**

A compact, stylish and discreet design that compliments any surveillance environment.

#### **DEPA**

The SNC-DH110T offers intelligent video analytics, based on the Sony DEPA platform. DEPA is a combined function of the intelligence built in to the camera and rules/filters that determine which images should be recorded or when an alarm should be triggered.

#### **EXMOR® and CMOS® Sensor**

High resolution CMOS® sensor with low noise characteristics for improved image acquisition. Derived from Sony's broadcast product range, EXMOR® is one of the highest quality image

sensors available.

### **Power over Ethernet (PoE) capability**

Supporting Power over Ethernet (PoE), the camera can be powered using the same Ethernet cable it uses for data transfer. This feature greatly reduces the physical infrastructure costs and speed of deployment.

### **ONVIF (Open Network Video Interface Forum) compliance**

The ONVIF (Open Network Video Interface Forum) defines a common protocol for the exchange of information between network video devices including automatic device discovery and video streaming. Allows interoperability between network video devices.

### **HD (720p) resolution**

Detailed 720p HD progressive images. Progressive acquisition (as opposed to interlace) means that images are more stable to view, contain more information and compress more efficiently - without "interlace artefacts".

### **Supports multiple industry standard codecs: H264, MPEG-4 and JPEG with dual streaming capability**

This multi-codec camera supports three compression formats: JPEG, the best choice of high-quality still images

### **Stream Squared Function**

An incredibly useful function that allows simultaneous streaming of two 4:3 aspect ratio videos in user-selectable SD resolutions. You can select the entire image or a portion of the image from the original view and resize to SD resolution. With this feature the SNC-DH110T can replace two SD cameras installed in the same line of view.

### **Electronic Day/Night**

Ensures that the camera is operating with the optimum sensitivity

for both day and night conditions.

## Analogue Monitor Output

This allows an analogue video monitor to be connected directly to the camera.

## Specifications

Camera	
Image Sensor	1/3.8-type CMOS sensor
Number of Effective Pixels	Approx. 1.3 Megapixels
Signal System	NTSC/PAL (switchable)
Sync System	Internal synchronization
Minimum Illumination (50 IRE)	Color: 5.5 lx (F2.8, AGC (Max.), 1/30 s)
Minimum Illumination (30 IRE)	Color: 3.0 lx (F2.8, AGC (Max.), 1/30 s)
Gain	Auto
Shutter Speed	1/2 s to 1/10,000 s
Exposure Control	Auto, EV Compensation, Auto Slow Shutter
White Balance	Auto(ATW, ATW-PRO) , Preset, One-push WB, Manual

Lens	Fixed lens
Zoom Ratio	Digital zoom 3x Total zoom 3x
Horizontal Viewing Angle	79°
Vertical Viewing Angle	62°
Viewing Tilt Angle	88°
Focal Length	f = 2.34 mm
F-Number	F2.8
Minimum Object Distance	500 mm

## Camera Features

Day/Night	Electronic D/N
e-Flip	YES
Noise Reduction	NR
Vandal Resistant	IK10
Superimpose Number	2 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo

	mark
Superimpose Language	English
Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese
Smartphone viewer	Yes
<b>Video</b>	
Resolution	1280x960, 1280x720, 1024x768, 1024x576, 768x576, 720x576, 704x576, 800x480, 720x480, 640x480, 640x368, 384x288, 352x288, 320x240, 320x192, 176x144
Compression Format	H.264, MPEG-4, JPEG
Maximum Frame Rate	H.264: 30 fps (1280x960) MPEG-4: 30 fps (1280x960) JPEG: 30 fps (1280x960)
Range of Bit Rate Setting	64K to 8 Mbps
Solid PTZ	Yes
Adaptive Rate Control	H.264

Bandwidth Control	JPEG
Multi streaming Capability	Dual streaming *1
Number of Clients	5

## Intelligent Video/Audio Analytics

Analytics Architecture	DEPA
Intelligent Motion Detection	Yes
Tamper Alarm	Yes

## System Requirements

Operating System	Microsoft Windows XP Windows Vista (32 bit) Windows 7 (32 bit, 64 bit)
Processor	Intel Core2 Duo 2 GHz or higher
Memory	1 GB or more
Web Browser	Microsoft Internet Explorer Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox Ver. 3.5 (plug-in free viewer only) Safari Ver. 4.0 (plug-in free viewer

only)  
 Google Chrome Ver.4.0 (plug-in free viewer only)

---

SNC toolbox	Yes
-------------	-----

---

SNC toolbox mobile	Yes
--------------------	-----

---

## Network

Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
-----------	--

---

Number of IP Address/Mac ADDRESS	1
----------------------------------	---

---

QoS	DSCP
-----	------

---

Multicast Streaming Support	Yes
-----------------------------	-----

---

ONVIF Conformance	Profile S
-------------------	-----------

---

Authentication	IEEE802.1X
----------------	------------

---

## Interface

Analog Monitor	AV MiniJack
----------------	-------------

---

## Output for Setup

Network Port	10BASE-T/100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x1

## General

Power Requirements	IEEE 802.3af compliant (PoE) Class 1
Power Consumption	2.4 W
Operating Temperature	0 to +50°C +32°F to +122°F
Storage Temperature	-20 °C to + 60 °C -4 °F to + 140 °F
Operating Humidity	20 % to 80 %
Storage Humidity	20 % to 95 %
Dimensions *2	φ106 x 50.5 mm φ4 1/4 x 2 inches
Mass	170 g (without cable)
External Material	Clear Dome cover: PC Top cover: AL Die-cast Lower case: PC+ABS



External Color      Top cover: Munsell 1.5B 1.97/0.34  
for Black model  
Top cover: Munsell 8.5GY 8.2/0.2  
for White Model

Safety Regulations      JATE Technical Standard (LAN)  
UL2044, IEC60950-1 (CB)  
VCCI Class B, FCC Class B, IC Class  
B  
Emission: EN55022 (Class B) +  
EN50130-4  
Immunity: EN55022 (Class B) +  
EN55024  
Emission: AS/NZS CISPR22 (Class  
B)

Supplied Accessories      Installation Manual (1)  
B&P warranty booklet (1)  
Sensor input cable (1)  
Template (1)

## Notes

\*1      Dual streaming (Any combination  
with JPEG/MPEG-4/H.264,  
including multiple streams of the  
same format)

\*2      The values for dimensions are

approximate.

---

## Gallery





