

4,000 lumens WUXGA 3LCD Basic
Installation projector with HDBaseT™
connectivity



Overview

A great fit for demanding middle and large classrooms and meeting rooms where cost is critical

Features

High resolution WUXGA image

High image quality 3LCD BrightEra™ natural and vivid colour images with high brightness of 4000 lumens

Fine lens shift: +/- 5%, Horizontal: +/- 4%

1.5:1 to 2.2:1 throw ratio


Connectivity via HDBaseT™*


Blend-in design


Advanced energy-saving features

Specifications

The table area consists of four teal-colored header bars, each followed by a series of horizontal lines representing rows in a table. The first teal bar is followed by one line. The second teal bar is followed by three lines. The third teal bar is followed by six lines. The fourth teal bar is followed by two lines.









Gallery

