

## BVML-T10

3D LUT output license for BVM-HX3110/HX1710/HX1710N

A black square icon with the words "SOFTWARE LICENSE" in blue, sans-serif capital letters.A yellow rectangular icon with the letters "HDR" in black, bold, sans-serif capital letters.

### Overview

The BVML-T10 is a 3D LUT output license for Sony's TRIMASTER HX master monitor, BVM-HX3110, HX1710 and HX1710N. This license can be used to output an SDI signal that is processed by a stored user 3D LUT data in the monitor. Our tetrahedral LUT interpolation in the monitors ensures the highest level of processing for the best possible final results. This feature is activated via USB port on the front control panel of the BVM-HX3110.

For BVM-HX1710/1710N, this function is activated via the USB port on the BVMK-R10.

You can use this feature to provide a 3D LUT applied signal to an external device in a system.

Quad-Link or Dual-link signals are automatically converted to appropriate single-link signals.

The BVML-H10 and BVML-S10 support this feature. When you have either of them, you do not need this license. When you only need the 3D LUT baked output feature with a signal conversion from 4K/UHD to 2K/HD, the BVML-S10 is the license for the purpose. When you need the 3D LUT output feature with both Sony's HDR-SDR conversion and the signal conversion, the BVML-H10 is the license for your requirement.

## Features

### User 3D LUT\*

This license supports the output of signals with applied User 3D LUTs via the Enhanced Monitor Output to other devices, further facilitating efficient workflows in live production, cinema, drama, commercial, music, and documentary production environments. Our tetrahedral LUT interpolation in the monitors ensures the highest level of processing for the best possible final results. Quad-Link or Dual-link signals are automatically converted to appropriate single-link signals.

\* BVML-T10 3D LUT output license available separately. HDR-SDR conversion is activated via the USB port of the front control unit.

## Related products



### **BVM- HX3110**

30.5-inch 4K  
TRIMASTER HX™  
Professional Master  
Monitor



### **BVM- HX1710**

16.5-inch 4K  
TRIMASTER HX™  
Professional Master  
Monitor



### **BVM- HX1710N**

16.5-inch 4K  
TRIMASTER HX™  
Professional Master  
Monitor

## Gallery

