

HDLA-1505/B

HD Large Lens Adaptor



Overview

The HDLA-1505/B allows operation of the HDC-1500 HD portable camera or HDC-3300 SuperMotion camera together with large studio/OB lenses and LCD viewfinders. Unlike traditional lens "build-up kits", the HDLA-1505/B provides a very simple one-touch cable-free mounting of the camera so that it can be quickly and easily converted from hand-held to tripod configuration.

Note

The HDLA-1505/B is finished in a dark grey body colour, the same as the HDC-1500 portable camera. If required, a pale coloured version, the HDLA-1505 is also available.

One-touch instant docking mechanism

The camera can be fitted quickly and easily into the adaptor. This unique mechanism allows the HDC-1500 to be attached and detached without removing the large lens.

Quick mounting for portable camera head

To provide efficient operation in studio or OB environments, the large lens adaptor has a unique design which allows the camera to be converted from hand-held to large lens configuration in just a few seconds.

Cable-free operation with all connections contained in "hot shoe" mounting

Utilizing a newly developed interlocking mechanism, power,

video, and control signals are passed on directly from the HDC-1500 to the HDLA-1505/B, without requiring additional cable connections.

Note that the HDVF-C730W viewfinder does require a conventional cable connection

Built-in teleprompter power supply

Utility power (200-240V AC) is available from the large lens adaptor, when used in conjunction with the HDCU-1000 camera control unit

Same handling characteristic as full size camera

All the control features and functionality traditionally associated with full size cameras are provided in this efficient operational package.

Compatible with HDVF-C730W colour LCD viewfinder

The HDLA-1505 is specifically designed to allow the HDVF-C730W to be mounted on the rear of the camera body. The 7" CRT viewfinder, HDVF-700A, cannot be used with this lens adaptor

Features

New low profile design with lower viewfinder height

Direct docking mechanism

Related products



HDCU-5000

Camera Control Unit

(CCU) for HDC-5500
and HDC-3500/3100
series system cameras

Gallery

