

## SNC-ER585

Outdoor Unitized 1080p/30 fps  
Rapid Dome Camera - E Series



### Overview

Sony SNC-ER585 is the ideal outdoor surveillance solution, rated IP66 (water proof) and IK10 (impact resistant) making it ideal for tough outdoor environments.

This camera delivers high quality 1080p Full HD images over a wide area of view with its superb pan, tilt and zoom capabilities. Its panning features high-speed 360 degrees endless rotation

### Features

**Fully integrated outdoor PTZ camera package, compatible with standard mounting solutions.**

**Full HD image sensor with x30 optical zoom**

**Water, dust and vandal resistant for reliable outdoor performance**

**High-speed 360 degrees endless rotation**

**Above-the-horizon tilt capability**

**Choose the compression format that suits your needs**

**Noise Reduction and Wide Dynamic Range, for challenging lighting conditions**

## Specifications

### Camera

Image Sensor	1/2.8-type Exmor CMOS sensor
Number of Effective Pixels	Approx. 3.27 Megapixels
Sync System	Internal synchronization
Minimum Illumination (50 IRE)	Color: 1.7 lx (F1.6, AGC On, 1/30 s, 50 IRE) B/W: 0.3 lx (F1.6, AGC On, 1/30 s, 50 IRE, Night Mode)
Minimum Illumination (30 IRE)	Color: 1.2 lx (F1.6, AGC On, 1/30 s, 30 IRE) B/W: 0.18 lx (F1.6, AGC On, 1/30 s, 30 IRE, Night Mode)
Dynamic Range	Theoretically 86 dB with DynaView Technology
S/N Ratio (Gain 0 dB)	More than 50 dB (Gain 0 dB)
Gain	Auto/Manual (-3 to +28 dB)
Shutter Speed	1/1 s to 1/10,000 s
Exposure Control	Full auto, Shutter priority, Iris priority, Manual
White Balance	Auto, Advanced Auto, ATW, Indoor, Outdoor, One-push, Manual,

	Sodium vapour lamp
Lens	Auto-focus zoom lens
Powered Zoom	Yes
Zoom Ratio	Optical zoom 30x Digital zoom 12x Total zoom 360x
Powered Focus	Yes
Auto Focus	Yes
Horizontal Viewing Angle	59.5° to 2.1°
Vertical Viewing Angle	33.4° to 1.2°
Focal Length	f = 4.3 mm to 129.0 mm
F-Number	F1.6 (Wide) to F4.7 (Tele)
Minimum Object Distance	300 mm (Wide) to 1200 mm (Tele)
Pan/Tilt Angle (powered)	360° endless rotation/210°
Pan Speed	300°/s (max.)
Tilt Speed	300°/s (max.)
Number of Preset	

Positions	256
-----------	-----

Number of Tour Programs	5
-------------------------	---

## Camera Features

Day/Night	True D/N
-----------	----------

Wide-D	Dyna View
--------	-----------

Noise Reduction	NR
-----------------	----

Image Stabilizer	Electronic
------------------	------------

Privacy Masking (number)	24
--------------------------	----

Privacy Masking (shape)	Quadrangle
-------------------------	------------

Privacy Masking (color/effect)	Opaque 14 colors (Black, White, Red, Green, Blue, Cyan, Yellow, Magenta, Gray (6 scales)), Mosaic
--------------------------------	---

Edge Storage	Yes
--------------	-----

Voice Alert	Yes
-------------	-----

Vandal Resistant	IK10
------------------	------

Ingress Protection	IP66
--------------------	------

Superimpose Number	3 independent positions for characters (Codec, Date & Time, Event, Text (Max. 64 characters)), 1 independent position for a logo mark
Superimpose Language	English
Menu Language	English, Japanese, Chinese (simplified), Chinese (traditional), French, Spanish, German, Italian, Korean, Portuguese, Russian, Arabic, Hindi, Vietnamese, Thai, Turkish, Polish
Smartphone viewer	Yes
<b>Video</b>	
Resolution	1920 x 1080, 1680 x 1056, 1280 x 1024, 1440 x 912, 1280 x 960, 1376 x 768, 1280 x 800, 1280 x 720, 1024 x 768, 1024 x 576, 800 x 600, 800 x 480, 768 x 576, 720 x 576, 704 x 576, 720 x 480, 640 x 480, 640 x 368, 384 x 288, 320 x 240, 320 x 192
Compression Format	H.264, MPEG-4, JPEG
	H.264: 30 fps (1920 x 1080) *1

Maximum Frame Rate	MPEG-4: 30 fps (1440 x 912) *1 JPEG: 30 fps (1440 x 912) *1
Bitrate Control Mode	CBR/VBR (selectable)
Range of Bit Rate Setting	64 Kbps to 8 Mbps
Adaptive Rate Control	H.264
Bandwidth Control	JPEG
Multi streaming Capability	Dual streaming *2
Number of Clients	5
Letter Box	Yes (1920x 1080 mode, aspect ratio: 16:9)

## Intelligent Video/Audio Analytics

Analytics Architecture	DEPA
Intelligent Motion Detection	Yes
Tamper Alarm	Yes
Advanced Audio Detection	Yes

## Audio

Compression Format    G.711/G.726

## System Requirements

Operating System	Windows XP (32 bit) Professional Edition Windows Vista (32 bit) Ultimate, Business Edition Windows 7 (32/64 bit) Ultimate, Professional Edition
Processor	Intel Core i7 2.8 GHz or higher
Memory	2 GB or more
Web Browser	Microsoft Internet Explorer Ver. 7.0, Ver. 8.0, Ver. 9.0 Firefox Ver. 3.5 (plug-in free viewer only) Safari Ver. 4.0 (plug-in free viewer only) Google Chrome Ver.4.0 (plug-in free viewer only)
SNC toolbox	Yes
SNC toolbox mobile	Yes

## Network

Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP, SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
Number of IP Address/Mac ADDRESS	1
QoS	DSCP
Multicast Streaming Support	Yes
ONVIF Conformance	Profile S
Authentication	IEEE802.1X

## Interface

Microphone Input	Mini jack (monaural), MIC IN: 2.5 V DC plug-in power
Line Output	Mini jack (monaural) Maximum output level: 1 Vrms
Network Port	10BASE-T/100BASE-TX (RJ-45)
Alarm Input (Sensor Input)	x2 (normally open/normally closed configurable)



Alarm Output	x2, AC 24V/DC 24V, 1 A (mechanical relay outputs electrically isolated from the camera)
Card Slots	SD x 1
Confirmed SD Card Type	SDHC (Max. 32 GB)

## General

Power Requirements	AC 24 V
Power Consumption	Heater ON: 76 W max., Heater OFF: 26 W max.
Operating Temperature	-40°C to +60°C -40°F to +140°F
Cold Start Temperature	-40°C to +60°C -40°F to +140°F
Storage Temperature	-20 °C to + 60 °C -4 °F to + 140 °F
Operating Humidity	20 % to 80 %
Storage Humidity	20 % to 95 %
Built-in Heater	Yes
Heater Working Temperature	5 °C or less 41 °F or less

Dimensions *3	<p>φ222.0 mm x 324.1 mm</p> <p>φ8 3/4 inches x 12 7/8 inches</p>
Mass	<p>Approx. 4.3 kg</p> <p>Approximate 9 lb 8 oz</p>
External Material	<p>Dome cover: PC</p> <p>Top sunshade: PC</p> <p>Coupling: ADC12</p> <p>Top cabinet: ADC12</p> <p>Sun shade: PC</p> <p>Dome flange: ADC12</p>
External Color	<p>Top sunshade: 6.4GY 8.0/0.3</p> <p>Coupling: 3.6GY 8.4/0.3</p> <p>Top cabinet: 3.6GY 8.4/0.3</p> <p>Sun shade: 6.4GY 8.0/0.3</p> <p>Dome flange: 3.6GY 8.4/0.3</p>
Safety Regulations	<p>JATE Technical standard (LAN)</p> <p>UL2044, IEC60950-1 (CB)</p> <p>VCCI (Class A), FCC (Class A), IC (Class A)</p> <p>Emission: EN55022 (Class A) + EN50130-4</p> <p>Immunity: EN55022 (Class A) + EN55024</p> <p>Emission: AS/NZS CISPR22 (Class A)</p> <p>C-Tick Class A</p>

Russia GOST-R  
KCC

---

Supplied Accessories	<p>Installation Manual (1)</p> <p>Dome cover (1)</p> <p>Top sunshade (1)</p> <p>Coupling (1)</p> <p>Wire fixing belt (1) (except China models)</p> <p>Wire bracket (1) (except China models)</p> <p>Bolts (2)</p> <p>Power supply connector (1)</p> <p>I/O harness (1)</p> <p>Harnes band (1)</p> <p>Band mount (1)</p>
----------------------	---

---

## Notes

*1	When using DynaView technology, the maximum frame rate becomes 15 fps
*2	Dual streaming (Any combination with JPEG/MPEG-4/H.264, including multiple streams of the same format)
*3	The values for dimensions are approximate.

---

## Related products



### **SNCA-POLE30**

Mounting pipe for pendant mount applications



### **SNCA-WM40**

Heavy duty outdoor wall mount for the SNC-RS84P, SNC-RS86P and SNC-RH164 rapid dome cameras



### **UNI-WMB3**

Wall mount bracket for PTZ dome mount security camera housings



### **SNCA-CEILING**

Mounting coupling for pendant applications

## Gallery

