

## ECM-77LM

Miniature omni-directional  
electret condenser microphone



### Overview

#### **Lavalier mic with excellent sound quality, ideal for use with DWT-B03R wireless transmitter**

The Sony ECM-77 miniature lavalier microphone is seen in daily use on TV shows around the world, and is an equally familiar sight in both studio-based productions and on location.

A discreet 'hands-free' alternative to handheld microphones, its popularity is due to a combination of excellent sound quality, robust construction and an attractive cosmetic design. The miniature design of the ECM-77 makes it easy to conceal in a stage performer's costume.

The electret condenser microphone's omni-directional capsule is optimised for clear speech pick-up, with an extended frequency response, impressive sensitivity and low handling noise.

Featuring a 3-pin Lemo connector, this ECM-77LM version is an ideal partner for use with the DWT-B03R DWX Series digital wireless microphone bodypack transmitter.

### Specifications

#### Audio Section

Electret Condenser

## Capsule Type

Frequency Response	40 Hz to 20 kHz
Directivity	Omni-directional
Sensitivity <sup>*[1]</sup> [7]	-39.0 dB
Output Impedance <sup>*</sup> [2] [7]	6.3k $\Omega$ $\pm$ 30%, Unbalanced
Dynamic Range	95 dB or more
Signal-to-Noise Ratio <sup>*[3]</sup>	64dB (typ.)
Inherent Noise <sup>*[4]</sup>	32 dB SPL or less
Induction Noise From External Magnetic Field <sup>*[5]</sup>	5 dB SPL or less
Wind Noise <sup>*[6]</sup>	40 dB SPL or less (with windscreen)
Maximum Input Sound Pressure Level <sup>*[7]</sup>	127 dB SPL

## General Section

Connector	Small 3-pin connector
-----------	-----------------------

Mic Cable	5.25 feet 1.6 m
Power Requirements	DC 3.0 V to 10.0V
Power Consumption	0.4 mA or less
Dimensions *[8]	φ5.6 X 12.5 mm (Mic head) φ1/4 X 1/2 inches (Mic head)
Mass	Approx. 1.5 g (without cable) Approx. 0.053 oz (without cable)
Supplied Accessories	Single/horizontal type tie clip (1) Metal-mesh type windscreen (1)
Optional Accessories	Wind screen pack Vertical clip pack Safety pin type clip pack Horizontal double-clip pack Horizontal single-clip pack ECM-77 accessory kit Colored wind screen kit Black windscreen for ECM-77

## Notes

\*[1] 0 dB = 1 V/Pa, at 1 kHz

\*[2] Output impedance at 1 kHz

\*[3] IEC 179,A-weighted, 1 kHz, 1 Pa.

## Notes

\*[4] 0dB = 20  $\mu$ Pa

\*[5] dB SPL/1E-7 T

\*[6] Wind noise at 2m/s (0 dB SPL = 20  $\mu$ Pa)

\*[7] Vdd : 5.5V, RL : 8.2k $\Omega$

\*[8] The values for dimensions are approximate.

---

## Related products



### **DWT-B03R**

DWX Series digital  
wireless microphone  
bodypack transmitter

## Gallery

