

## FW-65EZ20L

65” Professional display rated for 16/7 operation with essential professional functions



### Overview

#### **Business-friendly with easy content sharing, control and customisation**

Ideal for digital signage and corporate applications, the slim, easy-to-use FW-65EZ20L Professional Display adds impact to all your visual communications. Very high 4K picture quality with 350 nit screen brightness is complemented by simple setup, content sharing and networked control – ideal for today’s connected AV environments.

### Features

#### **Brilliant 4K image quality that’s seen by everyone**

Advanced Sony picture processing technologies ensure your content looks its best, while 350 nit panel brightness ensures clear visibility in indoor environments. The display’s wide viewing angle lets everyone in the room enjoy crisp, clear images wherever they’re positioned.

#### **Enjoy finer detail**

4K X-Reality PRO upscales pictures closer to true 4K quality. Images are sharpened and refined in real time, revealing extra detail from lower-resolution content.

#### **Vivid, natural colour**

Live Color technology brings images alive with a brilliant palette of vibrant, natural colours.

## **Smooth on-screen movement**

Motionflow XR ensures smoother, more natural reproduction of rapidly-moving on-screen images.

## **Great pictures deserve brilliant sound**

The slim design of FW-65EZ20L incorporates an X-Balanced Speaker™, offering clear voice quality to enhance video conferences and digital signage.

## **Portrait or landscape installation**

Install BRAVIA in portrait or landscape orientation to suit any corporate space.

## **Easy access side-mounted connections**

Signal connections, networking and other interfaces are conveniently side mounted for easy installation and access when the display's in portrait position.

## **Quick, easy setup**

Simple Pro Settings allows customisation of BRAVIA to suit the demands of any business or retail environment. Schedule power on/off times, select input source on switch on, wake up the display when an input signal's detected – and more.

## **Networked control**

Remotely control and monitor BRAVIA display functions – like power on/off, input source and volume – over IP networks or using familiar RS-232C protocols.

## **Signage made simple**

Built-in support for HTML5 makes it easy to display interactive signage content on BRAVIA without the need for a dedicated set-top box, media player or PC. The on-board BRAVIA Signage Free (BSF) 2.0 app automatically plays out HTML content including videos and photos from the display's internal 16GB storage, or when a USB stick memory is slipped into BRAVIA.

## Wireless screen mirroring

Easily mirror content wirelessly from handheld device onto BRAVIA with in-built support for Apple AirPlay and Google Chromecast.

## Sustainability in every scene

With growing demand for ever larger display screens, there is also the risk of greater resource and energy use. However, Sony’s sustainability commitments are realizing efficiency gains from product development right through to customers’ viewing screens.

## Specifications

General Features	
Screen Size	65"
Brightness (cd/m <sup>2</sup> )	350
Contrast Ratio	1,200:1
Dynamic Contrast Ratio	400,000:1
Response Time (ms)	8
Display Resolution (H x V, pixels)	3840 x 2160
HDR (High Dynamic Range) Compatibility	Yes (HDR10,HLG,Dolby Vision)
Aspect Ratio	16:9

Portrait/Tilt Compatibility	Yes
--------------------------------	-----

## Display Features

Dimming Type	Frame Dimming
--------------	---------------

Display Device	LCD
----------------	-----

Panel Type	IPS
------------	-----

Backlight Type	Direct LED
----------------	------------

Colour Gamut (DCI- P3)	75%
---------------------------	-----

Picture Processor	4K Processor X1
-------------------	-----------------

Operation Time	16/7
----------------	------

Deep Black Non-Glare Coating	No
---------------------------------	----

Haze (%)	1%
----------	----

Viewing Angle (Right/Left)	178 (89 / 89) degree (CR >10)
-------------------------------	-------------------------------

Viewing Angle (Up/Down)	178 (89 / 89) degree (CR >10)
----------------------------	-------------------------------

## Video Specification

Wide Mode	Auto / Wide zoom / Normal / Full / Full Pixel / Zoom / 14:9
-----------	---

4:3 Default	Yes
-------------	-----

Video Processing	4K X-Reality PRO
------------------	------------------

Motion Enhancer	Motionflow XR
-----------------	---------------

HDMI Signal	4096 x 2160p (24, 50, 60 Hz), 3840 x 2160p (24, 25, 30, 50, 60 Hz), 1080p (30, 50, 60 Hz), 1080/24p, 1080i (50, 60 Hz), 720p (30, 50, 60 Hz), 720/24p, 576p, 576i 480p, 480
-------------	--

## Audio Specification

Speaker Position	Down Firing
------------------	-------------

Audio Power Output	10W + 10W
--------------------	-----------

## Professional Features

Pro Mode	Yes (Simplified)
----------	------------------

---

HDMI Auto Wake-Up	Yes
-------------------	-----

---

Operating System	Android TV
------------------	------------

---

On-board Storage (GB)	16GB
-----------------------	------

---

## Network Specification

Wi-Fi Certified	Yes
-----------------	-----

---

Wireless LAN	Integrated
--------------	------------

---

## Convenience Features

USB Playback Codecs	MPEG1:MPEG1/MPEG2 PS:MPEG2/MPEG2, WEBM:AV1/AC4/ogg/AAC
---------------------	--

---

On Screen Clock	Yes
-----------------	-----

---

Sleep Timer	Yes
-------------	-----

---

On/Off Timer	Yes
--------------	-----

---

Chromecast Built-In	Yes
---------------------	-----

---

Apple AirPlay	Yes
---------------	-----

---

## Control Specifications

IP Control	Yes
------------	-----

---

RS-232C Control	Yes
-----------------	-----

---

HDMI-CEC	Yes
----------	-----

---

## Inputs and Outputs

HDCP	HDCP2.3 (for HDMI1/2/3/4)
------	---------------------------

---

Composite Video Input (s)	1 (Side, Mini jack)
---------------------------	---------------------

---

HDMI Inputs Total	3 (3 Side)
-------------------	------------

---

Analog Audio Input (s) (Total)	1 (Side Analog Conversion)
--------------------------------	----------------------------

---

Digital Audio Output (s)	1 (Side)
--------------------------	----------

---

USB Ports	2 (Side)
-----------	----------

---

Ethernet Inputs	1 (Side)
-----------------	----------

---

## Design Features

Frame Colour	Hairline Black
--------------	----------------

---

Stand Design	No Stand
--------------	----------

---

VESA® Hole Spacing Compatible	Yes
-------------------------------	-----

---

---

VESA® Hole Pitch (W x H)	300 x 300 mm / 11 7/8 x 11 7/8 inch
--------------------------	-------------------------------------

---

## Environment Specifications

Screen Size for WEB (diagonal, cm, integer or 1st decimal)	164 cm
---	--------

---

Rated Power Consumption	230 W
-------------------------	-------

---

Power Consumption (in Standby)	0.5 W
--------------------------------	-------

---

Dynamic Backlight Control	Yes
---------------------------	-----

---

Power Saving Mode	Yes
-------------------	-----

---

Power Consumption (Networked Standby) (for Saudi Arabia only)	2.00 W (Wi-Fi) / 2.00 W (Ethernet) / 2.00 W (HDMI)
---	--

---

Power Consumption (Off Mode) (for Saudi Arabia only)	Not applicable
--	----------------

---

Standby Mode Activated (Default) (for Saudi Arabia only)	Within 4 hours
--	----------------

---



Power Consumption (in standby with all network ports connected) (for Saudi Arabia only)	Less than 5.00 W
---	------------------

Wireless Network(s) On / Off Switch (Energy) (for Saudi Arabia only)	To turn on / off Wi-Fi, press HOME / MENU button on the remote control, then select [Settings] - [Network and Internet] - [Wi-Fi].
---	--

## Measurements

Dimension of TV without Stand (W x H x D)	1462 x 842 x 71 mm / 57 5/8 x 33 1/4 x 2 7/8 inch
---	---

Dimension of TV with Stand (W x H x D)	1462 x 842 x 71 mm / 57 5/8 x 33 1/4 x 2 7/8 inch
---	---

Dimension of Package Carton (W x H x D)	1588 x 965 x 184 mm / 62 5/8 x 38 x 7 1/4 inch
--	--

## Weight

Weight of TV without Stand	20.4 kg / 45 lb
-------------------------------	-----------------

Weight of TV with Stand	21.3 kg / 47 lb
----------------------------	-----------------

---

Weight of Package Carton (Gross)	28 kg / 61.7 lb
-------------------------------------	-----------------

---

## Accessories

Wall-Mount Adjuster (Bundled)	Yes (Depending on Region)
----------------------------------	---------------------------

---

## Related products



### **BRAVIA EZ20L Series**

Professional display  
rated for 16/7  
operation with  
essential professional  
functions; available in  
a full range of screen  
sizes

## Gallery



