

## UNI-OPL7C3

Outdoor Pressurized dome camera housing



### Overview

Applicable Camera Models;  
- SNC-RX550P - SNC-RX530P - SNC-RX570P Fixing Method;  
- SNCA-WM20G (wall) -SNCA-CEILING (ceiling) -SNCA-WM20FC (see note) Rating;  
-IP67 Operating Temperature;  
--29°C to +50°C (SNCA-HEATER) Voltage;  
-24 volts AC Optional accessories;  
-SNCA-CLEAR/2 (included)  
-SNCA-TINTED/2

### Related products



#### **SNC- EB600**

Box-type 720p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



#### **SNC- EB600B**

Basic Box-type  
720p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



#### **SNC- EB630**

Box-type 1080p/30 fps  
Camera Powered by  
IPELA ENGINE EX™ - E  
Series



#### **SNC- EB630B**

Basic Box-type  
1080p/30 fps Camera  
Powered by IPELA  
ENGINE EX™ - E Series



#### **SNC-**



#### **SNC-**



#### **SNC-**



#### **SNC-**

## **VB600**

Box-type 720p/60 fps  
Camera Powered by  
IPELA ENGINE EX™ - V  
Series



## **EP521**

Standard Definition  
(PAL) PTZ Network  
Camera



## **EP580**

1080p/30 fps PTZ  
Camera - E Series

## **ER521**

Standard Definition  
(PAL) Rapid Dome  
Network Camera

## **SNC- ER550**

720p/30 fps Rapid  
Dome Camera - E  
Series

## **SNC- ER580**

1080p/30 fps Rapid  
Dome Camera - E  
Series

## Gallery

