

VPL-EW235

2,700 lumens WXGA portable projector with wireless connectivity



Overview

Bring learning to life with this bright, energy-efficient, wireless-ready portable projector that has been designed in consultation with teachers and made for today's classrooms

Combining superb widescreen WXGA image quality with smart energy-efficient features, the VPL-EW235 portable projector enhances learning with powerful presentations that really stand out. Simple to use and wireless ready, the projector is ideal for maximising student engagement in today's networked classrooms, making it your ideal partner throughout the busy school day.

Sony BrightEra™ panel technology assures clear pictures in any conditions, from daylight to darkened classrooms. Plenty of interfaces allow easy connection, while a choice of Picture Modes optimises viewing with any source – slide presentations, PC documents, pictures or videos. Adding an optional Wi-Fi module lets students and teachers wirelessly share homework, images and graphics from mobile devices like smartphones and tablets. There's a wide range of smart energy-saving features built in. And with a recommended lamp replacement time of 10,000 hours, downtime and maintenance costs are minimised.

Features

Energy efficient with long-lasting lamp of 10,000 hours

The lamp driver optimally controls the wattage of the lamp and achieves a long-lasting lamp time of 10,000* hours. The recommended lamp replacement time is extended by 43%, compared to the previous model.

*Lamp mode: low, Complies with IEC61947 standard

Advanced energy-saving features

Advanced lamp technology enables robust energy-saving features. For example, greater brightness control in Auto Light Dimming mode saves considerable energy when the projector is left on without being used. During projection, Auto Lamp Mode automatically adjusts light output to suit the projected scene. When you need to mute the picture temporarily, light output can be completely deactivated to minimise energy consumption.

High image quality 3LCD BrightEra™ natural and vivid colour images

Widescreen WXGA (1280 x 800) 16:10 screen resolution, 3LCD BrightEra™ natural and vivid colour images, plus various Picture Modes for optimising image quality, make the projector one of the best in its class. Thanks to the optical system projecting three basic colours constantly, the projector offers excellent light efficiency, ensuring colourful and bright images. Sony's BrightEra™ panels deliver improved panel light resistance, higher resolution, high brightness and increased panel reliability. High colour reproducibility is important especially when using colourful content, such as materials used in classrooms.

Various picture modes for optimal picture quality

The projector has six available picture modes for correct picture quality: Dynamic, Standard, Presentation, Blackboard, Game, and Cinema. With six picture modes and three brightness modes combined, the user can select the most suitable

picture/brightness combination according to the picture source and environment, to create the optimal image.

Network presentation (LAN/Wireless LAN)

When the projector is installed in a LAN, presentations can be projected from any PC and Mac on the network. A tablet or smartphone can be connected at the same time. You can project jpg, pdf and other supported formats. Up to four users can project PC/Mac images simultaneously, while up to eight users can connect to one projector. For PC/Mac, an application, Projector Station for Network Presentation, is provided. For a tablet/smartphone, an application is provided by Pixelworks, downloaded from the web. For details, please visit: <http://PWPresenter.pixelworks.com>

Remote control for iOS device

Projector Remote is a simple remote control application for Sony's projectors. Networked projectors can be controlled by this remote application. Remote Control allows you to operate the projector with simple and easy-to-read buttons.

USB display

The projector allows you to display pictures and audio* with one USB cable. You do not need to install any driver for this function. It is a convenient way to connect to the projector when you want to connect easily.

* There is a time lag in video and audio. When not in simple use, it is recommended to use Line-in or HDMI-in.

Input Label

The input label, which appears in the input menu on screen, can be customised. This gives users a clear understanding of which equipment is connected.

Built-in speaker

The projector includes a 16W monaural speaker.

Specifications

Display System

| | |
|----------------|--------------|
| Display System | 3 LCD system |
|----------------|--------------|

Display device

| | |
|--------------------------------|--|
| Size of effective display area | 0.59" (15 mm) x 3 BrightEra LCD Panel, Aspect ratio: 16:10 |
|--------------------------------|--|

| | |
|------------------|---------------------------------|
| Number of pixels | 3,072,000 (1280x800 x 3) pixels |
|------------------|---------------------------------|

Projection lens

| | |
|-------|--------|
| Focus | Manual |
|-------|--------|

| | |
|-----------------------|--------|
| Zoom - Powered/Manual | Manual |
|-----------------------|--------|

| | |
|--------------|---------------|
| Zoom - Ratio | Approx. x 1.3 |
|--------------|---------------|

| | |
|-------------|------------------|
| Throw Ratio | 1.37:1 to 1.80:1 |
|-------------|------------------|

Light source

| | |
|------|----------------------------------|
| Type | Ultra high pressure mercury lamp |
|------|----------------------------------|

| | |
|---------|------------|
| Wattage | 210 W type |
|---------|------------|

Recommended lamp replacement time*1

Lamp mode: High 4000 H

Lamp mode: Standard 6000 H

Lamp mode: Low 10000 H

Filter cleaning / replacement cycle (Max.)*1

Filter cleaning /
replacement cycle 7000 H (cleaning)
(Max.)

Screen size

Screen size 30" to 300" (0.76 m to 7.62 m)
(measured diagonally)

Light output

Lamp mode: High 2700 lm

Lamp mode: Standard 1900 lm

Lamp mode: Low 1500 lm

Color light output

Lamp mode: High 2700 lm

Lamp mode: Standard 1900 lm

Lamp mode: Low 1500 lm

Contrast ratio (full white / full black)*2

Contrast ratio (full white / full black) 2700:1

Speaker

Speaker 16 W x 1 (monaural)

Displayable scanning frequency

Horizontal 14 kHz to 93 kHz

Vertical 47 Hz to 93 Hz

Display resolution

Computer signal input Maximum display resolution: UXGA 1600 x 1200 dots*3

Video signal input NTSC, PAL, SECAM, 480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, The following items are available for digital signal (HDMI input) only;

1080/60p, 1080/50p

Color system

Color system NTSC3.58, PAL, SECAM, NTSC4.43, PAL-M, PAL-N

Keystone correction (Max.)

Vertical +/-20 degrees

OSD language

OSD language 24-languages (English, Dutch, French, Italian, German, Spanish, Portuguese, Turkish, Polish, Russian, Swedish, Norwegian, Japanese, Simplified Chinese, Traditional Chinese, Korean, Thai, Vietnamese, Arabic, Farsi, Finnish, Indonesian, Hungarian, Greek)

INPUT OUTPUT (Computer/Video/Control)

INPUT A RGB / Y PB PR input connector:
Mini D-sub 15-pin (female)
Audio input connector: Stereo mini jack

| | |
|---------------|--|
| INPUT B | <p>RGB input connector: Mini D-sub 15-pin (female)</p> <p>Audio input connector: Stereo mini jack</p> |
| INPUT C | <p>HDMI input connector: HDMI 19-pin, HDCP support</p> |
| S VIDEO IN | <p>S video input connector: Mini DIN 4-pin</p> <p>Audio input connector: Pin jack (x2) (shared with VIDEO IN)</p> |
| VIDEO IN | <p>Video input connector: Pin jack</p> <p>Audio input connector: Pin jack (x2) (shared with S VIDEO IN)</p> |
| OUTPUT | <p>Monitor output connector*4: Mini D-sub 15-pin (female)</p> <p>Audio output connector*5: Stereo mini jack (variable out)</p> |
| REMOTE | <p>RS-232C connector: D-sub 9-pin (male)</p> |
| LAN | <p>RJ-45, 10BASE-T/100BASE-TX</p> |
| USB | <p>Type-A</p> |
| USB | <p>Type-B</p> |
| MICROPHONE IN | <p>Microphone jack: Mini Jack</p> |

Acoustic noise

Lamp mode: Low 30 dB

Operating temperature / Operating humidity

Operating temperature /
Operating humidity 0°C to 40°C (32°F to 104°F) / 35% to 85% (no condensation)

Storage temperature / Storage humidity

Storage temperature /
Storage humidity -20°C to +60°C (-4°F to +140°F) / 10% to 90% (no condensation)

Power requirements

Power requirements AC 100 V to 240 V, 3.0 A to 1.3 A, 50 Hz / 60 Hz

Power consumption

AC 100 V to 120 V Lamp mode: High: 289 W

AC 220 V to 240 V Lamp mode: High: 278 W

Power Consumption (Standby Mode)

| | |
|-------------------|---|
| AC 100 V to 120 V | 0.5 W (when “Standby mode” is set to “Low”) |
|-------------------|---|

| | |
|-------------------|---|
| AC 220 V to 240 V | 0.5 W (when “Standby mode” is set to “Low”) |
|-------------------|---|

Power Consumption (Networked Standby Mode)

| | |
|-------------------|---|
| AC 100 V to 120 V | 5.0 W (LAN) |
| | 5.6 W (optional WLAN module) |
| | 5.8 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard") |

| | |
|-------------------|---|
| AC 220 V to 240 V | 5.3 W (LAN) |
| | 5.9 W (optional WLAN module) |
| | 6.0 W (All Terminals and Networks Connected) (when "Standby Mode" is set to "Standard") |

Standby Mode / Networked Standby Mode Activated

| | |
|---|------------------------|
| Standby Mode / Networked Standby Mode Activated | After about 10 Minutes |
|---|------------------------|

Wireless Network(s) On/Off Switch

| | |
|--------------------------------------|--|
| Wireless Network(s) On/Off Switch | 1) Press the MENU button, then select [Connection/Power] 2) [WLAN Settings] 3) [WLAN Connection] 4) Select On or Off |
|--------------------------------------|--|

Heat dissipation

| | |
|-------------------|-----------|
| AC 100 V to 120 V | 986 BTU/h |
| AC 220 V to 240 V | 949 BTU/h |

Dimensions (W x H x D)

| | |
|---|--|
| Dimensions (W x H x D) (without protrusions) | Approx. 365 x 96.2 x 252 mm (14 3/8 X 3 25/32 X 9 29/32 inches) |
|---|--|

Mass

| | |
|------|-----------------------|
| Mass | Approx. 3.9 kg (8 lb) |
|------|-----------------------|

Supplied accessories

| | |
|------------------|--------|
| Remote commander | RM-PJ8 |
|------------------|--------|

Optional Accessories

| | |
|---------------|----------|
| Optional Lamp | LMP-E212 |
|---------------|----------|

| | |
|---------------------|----------|
| Wireless LAN module | IFU-WLM3 |
|---------------------|----------|

Notes

| | |
|----|---|
| *1 | This figure is expected maintenance time, not guaranteed time. The actual value depends on the environment and how the projector is used. |
|----|---|

| | |
|----|-----------------------|
| *2 | The value is average. |
|----|-----------------------|

| | |
|----|---|
| *3 | Available for VESA Reduced Blanking signal. |
|----|---|

| | |
|----|--------------------------|
| *4 | From INPUT A and INPUT B |
|----|--------------------------|

| | |
|----|--|
| *5 | Works as an audio switcher function. Output from a selected channel; not available in standby. |
|----|--|

| | |
|---|---|
| Environmental notice for customers in the USA | Lamp in this product contains mercury. Disposal of these materials may be regulated due to environmental considerations. For disposal or recycling information, please contact your local authorities or see www.sony.com/mercury for |
|---|---|

additional information.

Gallery

