

YT-ICB630

In-ceiling bracket designed for use with SNC W Series cameras



Overview

Secure mounting for use with the SNC-WR600/WR630 rapid dome camera

YT-ICB630 is used when the body of the camera is embedded in the ceiling, or with gypsum boards and similar, where the material used in the ceiling is too fragile to hold ordinary screws.

Strong in-ceiling bracket

Mass approx. 900g (2lb 3oz) including cover.

Features

Install camera on ceiling

Install the camera on the ceiling with the thickness from 10 mm to 35 mm (13/32 ~1 7/16 inches) inclusive.

Use with optional dome cover

The YT-ICB630 can be used with YT-LD124C/LD124S dome cover.

Gallery

