

AXS-A256S24

AXS Memory A Series card,
256 GB capacity, 2.4 Gbps
guaranteed write speed



Overview

Less power and more effective ventilation compared to previous AXS memory for RAW recording with AXS-R5 and AXS-CR1

The AXS-A256S24 AXS Memory (AXSM™) A Series card is an ultra high speed, high capacity, and high reliability flash memory media, for demanding 4K and 2K 16-bit linear RAW format, including High Frame Rate (HFR) recording up to 240fps in 2K resolution. The AXS-A256S24 has a capacity of 256 GB and guaranteed write speed of 2.4 Gbps. The card works with the AXS-R5 2K / 4K RAW recorder and AXS-CR1 USB 3.0 AXS Memory card reader, using the AXS Memory card adapter.

Slim and small design

35 x 75 x 8 mm size using less power and more effective ventilation compared to previous AXS Memory cards.

Ideal for PMW-F55, PMW-F5 and NEX-FS700 2K/4K RAW workflows

AXS Memory has a unique combination of capacity, sustained data throughput, security and portability. It opens up completely new ways for end-users to work.

Works with AXS-R5 and AXS-CR1

The AXS-A256S24 works with the AXS-R5 2K / 4K RAW recorder and AXS-CR1 USB 3.0 AXS Memory card reader,

using the AXS Memory card adapter.

Records 4K RAW, 2K RAW and 2K RAW HFR

High capacity recordings of, for example, 31 min 4K RAW and 121 min 2K RAW at 23.98PsF, 12 min 4K RAW and 49 min 2K RAW at 60p, and 12 min 2K RAW at 240fps (frames per second).

Features

High capacity, fast transfer speed recordings

The AXS-A256S24 has a capacity of 256 GB and guaranteed write speed of 2.4 Gbps.

Slim and small card design

The AXS-A256S24 has dimensions of 35 x 75 x 8 mm. This is smaller and lighter than previous AXS Memory cards and has same height and width dimensions as SxS Memory cards.

Less power usage

The AXS Memory A Series uses less power and provides more effective ventilation compared to previous AXS Memory cards.

Works with AXS-R5 and AXS-CR1

The AXS-A256S24 works with the AXS-R5 2K / 4K RAW recorder and AXS-CR1 USB 3.0 AXS Memory card reader, using the AXS Memory card adapter.*

* 1x AXS Memory card adapter supplied free to all existing and new AXS-R5 and AXS-CR1 customers. Additional adapters are available to purchase.

Records 4K RAW, 2K RAW at different frame rates

Capacity recordings of 31 min 4K RAW and 121 min 2K RAW at 23.98PsF, 24 min 4K RAW and 97 min 2K RAW at 29.97PsF, and 12 min 4K RAW and 49 min 2K RAW at

60p.

2K RAW HFR recordings

The AXS Memory A Series records High Frame Rate (HFR) recordings: 24 min 2K RAW at 120fps (frames per second), 16 min at 180fps and 12 min at 240fps.

Gallery

