

## BRBK-SF1

HD optical multiplex card for  
BRC-H900P and BRC-Z330  
robotic cameras



### Overview

**Allows transmission of HD signal up to 2,000 metres with BRU-SF10 HD optical multiplex unit**

The BRBK-SF1 interface card is designed for use for use with the BRC-H900P Full-HD robotic camera and the BRC-Z330 HD robotic camera. The combined use of this card, CCFC-S200200m single-mode optical fibre cable segments and BRU-SF10 HD optical multiplex unit allows up to 2,000 metres (6,562 feet) transmission of camera images, external video syncsignals, 2 analogue audio channels and control signals via optical fibre cable.

### Related products



#### **BRU-SF10**

HD/SD Optical Multiplex Unit for BRC-H900 and BRC-Z330 cameras



#### **BRC-Z330**

1/3-inch CMOS sensor SD / HD robotic camera

## Gallery

