

MDR-M1

New reference closed monitor headphones for creators with ultra-wideband playback.



Specifications

General	
Type	Closed dynamic
Driver Unit	40 mm (1.58 in)
Power Handling Capacity	1,500 mW (IEC *1)
Impedance	50 Ω at 1kHz
Sensitivity	102 dB/mW
Frequency Response	5 Hz - 80,000 Hz (JEITA)
Mass	Approx. 216 g (without cable)
Included Items	Headphones cable (approx. 1.2m/2.5 m, Stereo mini plug); Plug adaptor (Stereo standard plug - Stereo mini plug); Warranty card; Reference Guide
Notes	
*1	IEC International Electrotechnical Commission

Related products



MDR-MV1


Open back Studio Monitor Headphones for creating spatial and stereo sound with wide frequency range and soundstage feel



MDR-7506

Stereo professional headphones

Gallery



© 2004 - 2026 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. All trademarks are the property of their respective owners.