

## CAC-12

Adjustable camera microphone holder



### Overview

#### **Provides two-axis adjustment of microphone arm**

Allows microphone direction to be adjusted. For attaching the ECM-647/678 or the C-74 condenser microphone to cameras and camcorders.

#### **Multi camera compatible**

Can be used with: DSR-250P/1, DSR-400PK, DSR0400PL, DSR-400WSPL, DXC-D55PH, DXC-D55PK, DXC-D55PL, DXC-WSPL, DXC-D55WSPH.

### Features

#### **Multi camera compatible**

Can be used with these cameras: DSR-250P/1, DSR-400PK, DSR0400PL, DSR-400WSPL, DXC-D55PH, DXC-D55PK, DXC-D55PL, DXC-WSPL, DXC-D55WSPH.

#### **Holds a variety of microphones**

Includes rubber adapter for 19mm diameter microphones like the ECM-672 and C-74.

### Related products



## **HXC-FB80**

Three 2/3-inch  
Exmor™ CMOS sensor  
HD colour studio  
camera

## **HDLA- 3501**

Large Lens Adaptor

## **HDLA- 3505**

Large Lens Adaptor

## Gallery

