

LMP-C162

Replacement lamp for the VPL-CS20A/CX20A and VPL-ES3/EX3 LCD business projectors



Overview

165W UHP replacement lamp for the VPL-CS20A/CX20A and VPL-ES3/EX3 LCD business projectors

For the VPL-CS20A/CX20A and VPL-ES3 LCD business projectors.

Lamp replacement notification

A -inchplease replace the lamp-inch message is displayed when it is time to replace the lamp.

Features

Replacement lamp

For the VPL-CS20A/CX20A and VPL-ES3 LCD business projectors

Lamp replacement notification

The projector alerts you when the lamp needs to be replaced. A -inchplease replace the lamp-inch message is displayed when it is time to replace the lamp. The message disappears when any key on the remote commander or control panel is pressed.

Selectable lamp wattage

The lamp is switchable between 165W (High Mode) 125W (Std Mode) and lasts for 2000 hours.

Gallery

