

VPL-FHZ131L

13,000 lm (13,600 lm center)
laser light source projector
(colour availability may vary by
country)



Overview

Combining spectacular image quality with easy set-up and minimal maintenance needs, these high-brightness 3LCD laser projectors are ideal for installation in larger spaces.

Captivate your audience in conference halls, lecture theatres, galleries, museums, visitor attractions and other large spaces. A very high light output of 13,000 lumens ensures big-screen presentations with extra presence, even in brightly lit rooms.

Impressive picture quality is boosted by Sony's unique super resolution Reality Creation technology. This uses a powerful pattern-matching database to optimise lower-resolution images, enhancing clarity without increasing digital picture noise.

Save time with Sony's Intelligent Setting function that simplifies installation with pre-sets to optimise brightness, cooling, colour and other projector settings. You'll be rewarded with great pictures in every environment.

You'll appreciate an industry-leading lens shift adjustment range and a wide choice of interchangeable lenses, giving more options to install the projector in any space, including classrooms and halls with high ceilings. For extra flexibility the VPLL-Z4107 short throw lens is ideal when positioning the projector close to the screen to avoid ceiling-mounted obstructions.

Features

Reduced maintenance

The laser light source offers up to 20,000 hours* operation without lamp exchange, reducing maintenance needs compared with traditional projectors.

** Depending on usage environment.*

Consistent brightness

Experience consistent image brightness throughout the laser light source's 20,000 hours recommended lifespan.

Networked control and monitoring

Ideal for integration in AV environments with leading control, monitoring and management systems such as Crestron Connected™ and Extron® XTP™ Systems.*

** Extron and XTP Systems are trademarks of RGB Systems Inc.*

Easy edge blending

Seamlessly join colour-matched images from multiple projectors for stunning super-size displays in corporate and education environments.

Versatile lens options

There's a wide range of lens options to suit virtually any size of room and throw requirements. Quick-release bayonet mount simplifies lens exchange.

Generous lens shift range

Enjoy greater flexibility to position the projector in restricted spaces, ensuring that audience and presenters aren't distracted by the light source.

Lens position memory

Memorise and recall up to six settings for projected image size, position and aspect ratio, saving time in different environments.

(Requires optional VPLL-Z4111 lens)

Stylish blend-in design

The slim, stylish body features a flat top surface that blends discreetly into any space when the projector is ceiling mounted.

Specifications

Display System

Display System	3 LCD system
----------------	--------------

Display Device

Size of Effective Display Area	1" x 3 BrightEra LCD Panel, Aspect ratio: 16:10
--------------------------------	---

Number of Pixels	6,912,000 (1920 x 1200 x 3) pixels
------------------	------------------------------------

Aspect Ratio	16:10
--------------	-------

Resolution	WUXGA (1920 x 1200 pixels)
------------	----------------------------

Projection Lens

Focus	Powered / Manual (Depend on lens)
-------	-----------------------------------

Zoom - Powered / Manual	Powered / Manual (Depend on lens)
-------------------------	-----------------------------------

Zoom - Ratio	Depend on Lens
--------------	----------------

Throw Ratio	Depend on Lens
Lens Shift - Powered / Manual	Powered
Lens Shift - Range Vertical / Horizontal	Range Vertical: Depend on Lens Range Horizontal: Depend on Lens

Light Source

Type	Laser diode
------	-------------

Filter Replacement Cycle (Max.)

Filter Replacement Cycle (Max.)	10,000 H (service maintenance)
---------------------------------	--------------------------------

Screen Size

Screen Size	Depend on Lens
-------------	----------------

Light Output *1

Mode: Standard	13,000lm *2 / 13,600lm (Center)*3
Mode: Middle	10,000lm
Mode: Low	8,600lm

Colour Light Output *1

Mode: Standard	13,000lm
----------------	----------

Mode: Middle	10,000lm
--------------	----------

Mode: Low	8,600lm
-----------	---------

Contrast Ratio*1

Contrast Ratio (full white / full black)	Contrast Ratio (full white / full black) : ∞ : 1
--	---

Colour Space

Colour Space	sRGB 100% (Picture mode: sRGB)
--------------	--------------------------------

Displayable Scanning Frequency

Horizontal	15 kHz to 92 kHz
------------	------------------

Vertical	48 Hz to 92 Hz
----------	----------------

Accepted Signal Resolution

Computer Signal Input	Maximum signal resolution: 1920 x 1200
-----------------------	--

480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i,

Video Signal Input	1080/50i The following items are available for digital signal only; 1080/60p, 1080/50p, 1080/24p, 1080/30p *4
--------------------	--

Keystone Correction (Max.)

Horizontal	+/- 30 degrees
------------	----------------

Vertical	+/- 30 degrees
----------	----------------

INPUT OUTPUT (Computer/Video/Audio/Control)

INPUT A	RGB / Y PB PR input connector: 5 BNC (female)
---------	---

INPUT B	RGB input connector: Mini D-sub 15-pin (female)
---------	---

INPUT C	DVI input connector: DVI-D 24-pin (single link), HDCP support HDCP: v1.4
---------	---

INPUT D	HDMI input connector: HDMI 19-pin, HDCP support HDCP: v1.4
---------	---

INPUT E	HDBaseT interface connector: RJ45, 3 play
---------	---

INPUT F	Optional adaptor slot for 3G-SDI Input Adaptor (BKM-PJ20)
INPUT G	HTML Viewer
OUTPUT 1	Monitor output for Input A/Input B Connector: Mini D-sub 15-pin (female)
USB-1	Type-A x 1
USB-2	Type-B x 1 (for service)
REMOTE	D-sub9pin male/RS232C
LAN	RJ45, 10BASE-T/100BASE-TX/1000BASE-T

Acoustic Noise *1

Light Output Mode: Standard	42dB
--------------------------------	------

Light Output Mode: Middle	39dB
------------------------------	------

Operating Temperature / Operating Humidity

Operating Temperature /	0°C to 45°C (32°F to 109°F) / 20% to
-------------------------	--------------------------------------

Operating Humidity	80% (no condensation)
--------------------	-----------------------

Storage Temperature / Storage Humidity

Storage Temperature	-10°C to +60°C (14°F to +140°F) /
/ Storage Humidity	20% to 80% (no condensation)

Power Requirements

Power Requirements	AC 100 V to 240 V, 10.8 A to 4.4 A, 50 Hz / 60 Hz
--------------------	---

Power Consumption (Maximum)

AC 100 V to 120 V	1076W
-------------------	-------

AC 220 V to 240 V	1033W
-------------------	-------

Power Consumption (Standby Mode)

AC 100 V to 120 V	0.50W (when “Standby mode” is set to “Low”)
-------------------	---

AC 220 V to 240 V	0.50W (when “Standby mode” is set to “Low”)
-------------------	---

Power Consumption (Networked Standby Mode)

AC 100 V to 120 V	21.6W (LAN) 26.5W (HDBT) 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	---

AC 220 V to 240 V	21.3W (LAN) 26.5W (HDBT) 26.6W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")
-------------------	---

Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	Approx. 2 Minutes
---	-------------------

Heat Dissipation

AC 100 V to 120 V	3671 BTU/h
-------------------	------------

AC 220 V to 240 V	3524 BTU/h
-------------------	------------

Dimensions (W x H x D) (without protrusions)

Dimensions (W x H x D)	Approx. 544 x 205 x 564 mm
------------------------	----------------------------

DIMENSIONS (W x H x D) Approx. 544 x 203 x 564 mm
 (without protrusions) (21 13/32 x 8 1/16 x 22 7/32 inches)

Mass

Mass Approx. 27 kg (58 lb)

Supplied Accessories

Remote Commander RM-PJ30

Projection Lens

Projection Lens VPLL-Z4107, 4008, Z4111, Z4015,
 Z4019, Z4025, Z4045

Optional Projection Lens

VPLL-Z4107 Throw Ratio: 0:75:1 to 0:94:1
 Lens Shift - Range Vertical: +/-50%
 Lens Shift - Range Horizontal:
 +/-24%

VPLL-4008 Throw Ratio: 1:00:1
 Lens Shift - Range Vertical: +/-32%
 Lens Shift - Range Horizontal:
 +/-15%

Throw Ratio: 1:30:1 to 1:96:1
 Lens Shift - Range Vertical: +/-99%

VPLL-Z4111	Lens Shift - Range Horizontal: +/-51%
VPLL-Z4015	Throw Ratio: 1:85:1 to 2:44:1 Lens Shift - Range Vertical: +/-98% Lens Shift - Range Horizontal: +/-51%
VPLL-Z4019	Throw Ratio: 2:41:1 to 3:07:1 Lens Shift - Range Vertical: +/-107% Lens Shift - Range Horizontal: +/-57%
VPLL-Z4025	Throw Ratio: 3:02:1 to 5:58:1 Lens Shift - Range Vertical: +/-107% Lens Shift - Range Horizontal: +/-57%
VPLL-Z4045	Throw Ratio: 5.56:1 to 7.5:1 Lens Shift - Range Vertical: +/-107% Lens Shift - Range Horizontal: +/-57%

Notes

The figures are approximate. They

*1 vary depending on the environment or how the projector is used.

*2 The value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary depending on use conditions and environments.

*3 The value is light output measured at center area of screen in Standard mode, and average of all products shipped.

*4 When using BKM-PJ20

Gallery

