

## VPL-GTZ1

2,000 lumens 4K SXRD Ultra  
Short Throw Laser Light Source  
projector



### Overview

#### **4K, laser light source and ultra-short throw capabilities designed for a range of B2B and commercial applications**

The VPL-GTZ1's imaging technology combines Sony's proven 4K SXRD™ with a laser phosphor light source. The result is 2,000 lumens colour brightness and superb picture quality. The projector can throw high-resolution images up to approximately 147-inches (3.7m) diagonal and zoom down to 66-inches (1.7m)\*, achieved by respective 6.7-inch and zero inch (170mm ~ zero) distance\*\* from screen, across onto any white plane surface. The ultra-short throw will allow you to stand closer to the screen which will be beneficial for presentation application and also, being able to check details of the 4K image at closer distance without shading off the image. Its stylish, 'blend-in' design fits nearly any installation environment, and a low fan noise ensures quiet operation that won't disrupt user's experience. The projector's flexible installation and operation allows it to be floor-standing, ceiling-mounted or used for rear projection. Users can blend\*\*\* multiple projectors and a quick turn on/off feature is convenient for a wide range of applications.

Like Sony's other laser light source projectors, the VPL-GTZ1 can deliver an expected 20,000 hours of operation without the need

for a lamp exchange. This translates to substantial savings in time and money, reducing the costs normally associated with bulb replacement.

\* When projecting in 17:9 format

\*\* Measurement from screen to edge of width the product

\*\*\* Blending requires 3rd party software.

## Features

### **4K native resolution: More than 4x Full HD images**

The VPL-GTZ1 Professional 4K SXRD™ Projector offers native 4096 x 2160 resolution, which is more than four times the resolution of Full HD. The projector's newest generation 0.74" 4K SXRD panels have been developed utilising cumulative expertise delivering 4K display products to visualisation, simulation, and the digital cinema market.

### **Laser phosphor light source**

The VPL-GTZ1 combines the 4K SXRD display technology with a highly efficient laser phosphor light source. This unique combination delivers exceptionally bright, pictures with excellent colour accuracy and stability, plus high efficiency and significantly greater durability for reduced total cost of ownership.

### **2,000 lumens brightness**

Add more detail, impact and realism with high 2,000 lumens brightness, ideal for a range of B2B and commercial applications, including museums, design simulation, signage, oil and gas, simulation and training, corporate, and video wall applications.

### **Ultra short throw projection**

The projector can throw high-resolution images up to approximately 147-inches (3.7m) diagonal and zoom down to 66-inches (1.7m)\*, achieved by respective 6.7-inch and zero inch (170mm ~ zero) distance\*\* from screen, across onto any white plane surface. The ultra-short throw allows you to stand closer to

the screen, ideal for presentation applications and to be able to check details of the 4K image at closer distance without shading off the image.

\* When projecting in 17:9 format

\*\* Measurement from screen to edge of width the product

## **Up to 20,000\* hours operation with virtually no maintenance**

The advanced laser light source offers a typical 20,000 hours operation without maintenance or replacement, reducing lifetime running costs compared with traditional projectors. 20,000 hours filter replacement cycles keep the projector in peak operating condition while reducing maintenance trips even further.

\* Actual hours may vary depending on usage.

## **Create super-size displays with Edge Blending**

Seamlessly join accurately from multiple projectors, simplifying creation of stunning super-size displays for retail, corporate and live event applications (using 3rd party edge blending solution).

## **Flexible installation capabilities**

The projector's flexible installation and operation allows it to be floor-standing, ceiling-mounted or used for rear projection.

## **3D capabilities**

The projector offers 2K 3D with resolution up to 1920 x 1080. Optional accessories include TDG-BT500A 3D glasses (not included).

## **Low fan noise level**

The low fan noise ensures quiet operation.

## **HDMI inputs**

The projector has 4 x HDMI (4K 60p YCbCr 4:2:0 support) inputs.

## Specifications

### Display system

Display system	SXRD projection system
----------------	------------------------

### Display device

Size of effective display area	0.74" x 3 SXRD
--------------------------------	----------------

Number of pixels	26,542,080 (4096 x 2160 x 3) pixels
------------------	-------------------------------------

### Projection lens

Focus	Powered
-------	---------

Zoom - Powered/Manual	Powered
-----------------------	---------

Zoom - Ratio	Approx. x 1.6
--------------	---------------

### Light source

Type	Laser diode
------	-------------

### Screen size

Screen size	66" to 147" (1.67 m to 3.73 m) (measured diagonally)
-------------	---

## Light output

Lamp mode: High      2000 lm

---

## Color light output

Lamp mode: High      2000 lm

---

## Contrast ratio \*1

Contrast ratio      ∞:1 (Dynamic Contrast)

---

## Signal

Accepted digital signals\*1      VGA, SVGA, XGA, WXGA(1280x768), QuadVGA, SXGA, SXGA+

---

Video signal input      480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i, 1080/60p, 1080/50p, 1080/24p, 3840x2160/24p, 3840x2160/25p, 3840x2160/30p, 3840x2160/50p\*2, 3840x2160/60p\*2, 4096x2160/24p, 4096x2160/25p, 4096x2160/30p, 4096x2160/50p\*2, 4096 x 2160/60p\*2

---

## INPUT OUTPUT (Computer/Video/Control)

HDMI      HDMI (A)

---

HDMI	HDMI (x4)
REMOTE	RS-232C connector: D-sub 9-pin (female)
LAN	RJ-45, 10Base-T/100BASE-TX
IR IN	Mini Jack
USB	Type A, DC 5V, Max. 500 mA

## Acoustic noise

Lamp mode: Low	26 dB
----------------	-------

## Operating temperature (Operating humidity)

Operating temperature (Operating humidity)	5°C to 35°C (41°F to 95°F) / 35% to 85% (no condensation)
--	---

## Storage temperature (Storage humidity)

Storage temperature (Storage humidity)	-20°C to +60°C (-4°F to +140°F) / 10% to 90% (no condensation)
--	--

## Power requirements

Power requirements	AC 100 V to 240 V, 5.9 A to 2.5 A, 50 Hz / 60 Hz
--------------------	--

## Power consumption

Power consumption	520 W
Standby	0.4 W (when "Remote Start" is set to "Off")
Networked Standby	0.6 W (LAN) (when "Remote Start" is set to "On") When a LAN terminal is not connected, it becomes a low power consumption mode (0.5 W).

## Standby Mode / Networked Standby Mode Activated

Standby Mode / Networked Standby Mode Activated	After about 10 Minutes
---	------------------------

## Dimensions (W x H x D)

	1,250 mm × 265 mm × 535 mm (49.2 inches × 10.4 inches × 21.1 inches)
Dimensions (W x H x D)	1,100 mm × 265 mm × 535 mm (43.3 inches × 10.4 inches × 21.1 inches) (without handle)

## Mass

	Approx. 55kg (121 lb)
Mass	Approx. 50kg (110 lb) (without handle)

---

## Optional accessories

RF 3D Glasses	TDG-BT500A
---------------	------------

---

## Notes

*1	60p,30p,24p include 59.94/60Hz, 29.97Hz/30Hz, 23.98Hz/24Hz
----	--

---

*2	YCbCr 4:2:0 / 8 bit format signal
----	-----------------------------------

---



## Gallery

