

ZRA-T1

Optical transmitter for Crystal LED large display solutions



Overview

Greater system configuration flexibility with 300 m of connectivity

The ZRA-T1 offers a new, flexible solution. The ZRA-T1 converts signals from the ZRCT-300 RJ45 to an optical signal, sending this to the ZRA-R1 via an optical fibre cable over distances of up to 300 m.

Specifications

Supported Model

Cabinet

ZRD-B-series/C-series
ZRD-BH-series/CH-series

Controller

ZRCT-300

Type

Optical transmitter

Interface

Input	RJ45 x3
-------	---------

Output	SFP+ (multi-mode optical fiber)
--------	---------------------------------

Transmission

Fiber Optic	300 m (maximum)
-------------	-----------------

Support Signal Resolution

up to 1920x1080 (Full HD)
(4 pair required for 4K screen)

Dimensions

W x D x H (mm)	110 x 142.5 x 33.5 mm
----------------	-----------------------

Mass

(g)	610 g
-----	-------

Power *1

Power Requirement	DC 5V / 2A
-------------------	------------

Power Consumption	10W
-------------------	-----

Type of Terminal	USB Type-C
------------------	------------

Operating Temperature

0°C - 45°C (32°F~113°F)

Storage Temperature

-20°C - 60°C (4°F~140°F)

Operating Humidity

20-80% (No condensation)

Storage Humidity

20-80% (No condensation)

Notes

*1

Please use a USB AC adapter that is USB PD compliant.

Operation is not guaranteed with all USB AC adapters.

Related products



ZRA-R1

Optical receiver for
Crystal LED large
display solutions

Gallery

