

# ODBK-203

Base unit for Optical Disc Archive ODS-L30M PetaSite scalable library



## Overview

**The ODBK-203 is a base unit of power supply for the ODS-L60E.**

**The ODBK-20X series can drive the ODS-D280F and the ODS-D77F.**

### A world of solutions

You'll find Optical Disc Archive solutions from Sony at work in a wide range of environments where speedy, reliable access to your precious data is crucial - along with effortless scalability and attractive ownership costs. Optical Disc Archive provides archiving solutions across seven key industries, from digital Media Asset Management to healthcare, banking, education and more.

See our ODA solutions page or contact us now to see how ODA solutions can boost the profitability of everyone's business.

## Accessories



### ODS-D77F

Optical Disc Archive fibre channel drive unit for ODS-L30M PetaSite scalable library with transfer speeds up to 1,150 Mbps (read) and 780 Mbps (write-once disc) or 310 Mbps (rewritable disc)



### ODS-D280F

Optical Disc Archive fibre channel drive unit for the ODS-L30M/L60E/L100E PetaSite scalable library with very high transfer speeds of 1Gbps write (verify on) and 2Gbps read using ODC-3300R Generation 2 cartridge



### ODS-L100E

PetaSite Optical Disc Archive library expansion unit (cartridge only)



### ODS-L30M

PetaSite Optical Disc Archive 30-slot master library unit



### ODS-L60E

PetaSite Optical Disc Archive library expansion unit (drive and cartridge)

## Gallery

